



Arrow ECS Finland Oy - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS Finland Oy, Lars Sonckin kaari 16, 02600 Espoo, Finland

Email: education.ecs.fi@arrow.com

Phone: 0870 251 1000



Supervised Learning: Classification

CODE:	LENGTH:	PRICE:
W7103G	11.04 Hours	€380.00

Description

This course introduces you to one of the main types of modeling families of supervised Machine Learning: Classification. You will learn how to train predictive models to classify categorical outcomes and how to use error metrics to compare across different models. The hands-on section of this course focuses on using best practices for classification, including train and test splits, and handling data sets with unbalanced classes.

Objectives

By the end of this course you should be able to:- Differentiate uses and applications of classification and classification ensembles.
- Describe and use logistic regression models.- Describe and use decision tree and tree-ensemble models.
- Describe and use other ensemble methods for classification.
- Use a variety of error metrics to compare and select the classification model that best suits your data.
- Use oversampling and undersampling as techniques to handle unbalanced classes in a data set.

Audience

This course targets aspiring data scientists interested in acquiring hands-on experience with Supervised Machine Learning Classification techniques in a business setting.

Prerequisites

To make the most out of this course, you should have familiarity with programming on a Python development environment, as well as fundamental understanding of Data Cleaning, Exploratory Data Analysis, Calculus, Linear Algebra, Probability, and Statistics.

Programme

1. Logistic Regression
2. K Nearest Neighbors
3. Support Vector Machines
4. Decision Trees
5. Ensemble Models
6. Modeling Unbalanced Classes

Session Dates

Aikataulutamme kiinnostuksen mukaan. [Ota yhteyttä](#)

Additional Information

[This training is also available as onsite training. Please contact us to find out more.](#)