

Arrow ECS Finland Oy - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS Finland Oy, Lars Sonckin kaari 16, 02600 Espoo, Finland

Email: education.ecs.fi@arrow.com Phone: 0870 251 1000

■ NetApp NetApp SnapCenter Administration

CODE: LENGTH: PRICE:

NEP SNAP-C-ADM 24 Hours (3 days) €3,060.00

Description

This course focuses on the deployment of NetApp® SnapCenter® Server 4.4. You learn how to install, monitor, and manage SnapCenter Server. The course also discusses installation and use of licenses and role-based access control. You learn how to prepare hosts, install SnapCenter Plug-ins, and connect to NetApp ONTAP® AFF and FAS storage systems. You also review backup and restore of Windows file system data and the configuration of SnapMirror® and SnapVault® relationships for use with SnapCenter software. The course materials include an exercise workbook that serves as an on-the-job reference guide.

Objectives

This course focuses on enabling you to do the following:

- Explain the benefits and relationships between the various components of the SnapCenter solution
- Describe the methods to install the SnapCenter Server software
- Perform SnapCenter configuration of role-based access control, installation of licenses, and connections to storage VMs (storage virtual machines, also known as SVMs)
- Configure hosts and SnapCenter Server Plug-in packages
- Prepare data protection relationships for SnapCenter software
- · Perform backup and restore of Windows data
- · Explain monitoring and managing capabilities of SnapCenter Server

Audience

- NetApp and NetApp Partner Professional Services
- · Systems Engineers
- NetApp Customers

Prerequisites

The SnapCenter Fundamentals elearning training should be undertaken prior to this class. This is delivered free of charge via the NetApp Learning Center. Please contact us via the link below for any additional support..

Contact Us

Programme

Module 1: SnapCenter Software Review

Introduction to the SnapCenter Suite
Server architecture
Plug-in Packages
licensing
Management Interfaces
Integration with ONTAP features

Module 2: SnapCenter Server Deployment

Server Installation Workflow Server Requirements

Additional Installation Options

Module 3: SnapCenter Server Configuration

License Management
Server Connections to the Storage System
Server RBAC

Module 4: Preparing Hosts for SnapCenter

Add Hosts to the SnapCenter Server Installing Plug-in Packages

Module 5: Assigning NetApp Storage to Windows Hosts

Configuring LUN storage on Windows Windows Disk Management Working with SMB Shares

Module 6: Preparing Data Protection Relationships for SnapCenter

Data protection relationships with SnapCenter Preparing the storage systems for replication

Module 7: Data Backup and Restore

Backup of Windows file systems Restore of Windows file systems Cloning Windows file system backups

Module 8: Monitoring and Managing with the SnapCenter server

Managing the SnapCenter Repository Monitoring Activities Understanding SnapCenter Reporting Features

Labs:

Storage configuration
SnapCenter server configuration
Plug-in configuration, installation and monitoring
Storage configuration
SnapMirror and SnapVault configuration
SnapCenter backup, restore and clone fundamentals
Monitoring and managing SnapCenter software

Session Dates

Date	Location	Time Zone	Language	Туре	Guaranteed	PRICE
26 Jan 2026	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00
05 May 2026	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00
01 Sep 2026	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00
02 Nov 2026	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00

Additional Information

This training is also available as onsite training. Please contact us to find out more.