



Arrow ECS Finland Oy - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS Finland Oy, Lars Sonckin kaari 16, 02600 Espoo, Finland

Email: education.ecs.fi@arrow.com

Phone: 0870 251 1000



NetApp SnapCenter Administration

CODE:	LENGTH:	PRICE:
NEP_SNAP-C-ADM	24 Hours (3 days)	€3,060.00

Description

This course focuses on the deployment of NetApp® SnapCenter® Server 4.4. You learn how to install, monitor, and manage SnapCenter Server. The course also discusses installation and use of licenses and role-based access control. You learn how to prepare hosts, install SnapCenter Plug-ins, and connect to NetApp ONTAP® AFF and FAS storage systems. You also review backup and restore of Windows file system data and the configuration of SnapMirror® and SnapVault® relationships for use with SnapCenter software. The course materials include an exercise workbook that serves as an on-the-job reference guide.

Objectives

This course focuses on enabling you to do the following:

- Explain the benefits and relationships between the various components of the SnapCenter solution
- Describe the methods to install the SnapCenter Server software
- Perform SnapCenter configuration of role-based access control, installation of licenses, and connections to storage VMs (storage virtual machines, also known as SVMs)
- Configure hosts and SnapCenter Server Plug-in packages
- Prepare data protection relationships for SnapCenter software
- Perform backup and restore of Windows data
- Explain monitoring and managing capabilities of SnapCenter Server

Audience

- NetApp and NetApp Partner Professional Services
- Systems Engineers
- NetApp Customers

Prerequisites

The SnapCenter Fundamentals elearning training should be undertaken prior to this class. This is delivered free of charge via the NetApp Learning Center. Please contact us via the link below for any additional support..

[Contact Us](#)

Programme

Introduction to the SnapCenter Suite
 Server architecture
 Plug-in Packages
 licensing
 Management Interfaces

Module 1: SnapCenter Software Review

Integration with ONTAP features
 Server Installation Workflow
 Server Requirements
 Additional Installation Options

Module 2: SnapCenter Server Deployment

License Management
 Server Connections to the Storage System
 Server RBAC

Add Hosts to the SnapCenter Server

Module 4: Preparing Hosts for SnapCenter

Installing Plug-in Packages
 Configuring LUN storage on Windows
 Windows Disk Management

Module 5: Assigning NetApp Storage to Windows Hosts

Working with SMB Shares
 Data protection relationships with SnapCenter

Module 6: Preparing Data Protection Relationships for SnapCenter

Preparing the storage systems for replication
 Backup of Windows file systems
 Restore of Windows file systems

Module 7: Data Backup and Restore

Cloning Windows file system backups
 Managing the SnapCenter Repository
 Monitoring Activities

Module 8: Monitoring and Managing with the SnapCenter server

Understanding SnapCenter Reporting Features
 Labs:
 Storage configuration
 SnapCenter server configuration
 Plug-in configuration, installation and monitoring
 Storage configuration
 SnapMirror and SnapVault configuration
 SnapCenter backup, restore and clone fundamentals
 Monitoring and managing SnapCenter software

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
13 Jan 2025	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00
07 Apr 2025	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00
14 Jul 2025	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00
26 Aug 2025	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00
13 Oct 2025	Virtual Classroom (GMT / UTC)		English	Instructor Led Online		€3,060.00

Additional Information

This training is also available as onsite training. Please contact us to find out more.