



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS B.V., Kromme Schaft 5, 3991 AR Houten, The Netherlands

Email: education.ecs.nl@arrow.com

Phone: +31 20 582 6109



IBM Sterling File Gateway Managing Sterling File Gateway

CODE:	LENGTH:	PRICE:
ODC6000G	16 Hours (2 days)	€1,560.00

Description

This 2-day course introduces the student to the Sterling File Gateway functionality and provides the specific technical skills needed to deploy and support it. The course provides an overview of the features and provides hands-on exercises for creating routing templates, transforming file names, searching for files within a route, and reporting on file transfers.

Objectives

After completing this course, students should be able to:

- Install and configure Sterling File Gateway.
- Describe community, groups and users.
- Build static and dynamic routing channel templates.
- Describe the different persona's and their responsibilities.
- Configure routing channels.
- Transfer file from a producer to a consumer.
- Broadcast messages.
- Explain the enhanced visibility to track a route.
- Explain container and non-container layers.
- Generate reports.
- Discuss the procedure for Sterling File Gateway extensibility.

Audience

This course is designed for administrative users who administer the Sterling File Gateway application.

Prerequisites

Before taking this course, students should have a working knowledge of:

- IBM® Sterling B2B Integrator

Programme

UNIT 1. OVERVIEW OF STERLING FILE GATEWAY

- Lesson 1. Introduction
- Lesson 2. Users and Trading Partners
- Lesson 3. Route Channel Templates (RCT)
- Lesson 4. Mailbox Management
- Lesson 5. Static Route

UNIT 2. IMPLEMENTATION

- Lesson 1. Dynamic Route
- Lesson 2. File Layers
- Lesson 3. Reports
- Lesson 4. Extensibility

Course Wrap Up

Session Dates

On request. Please [contact us](#)

Additional Information

[This training](#) is also available as onsite training. Please contact us to find out more.