



**Enterprise Computing Solutions - Education Services**

## **TRAINING OFFERING**

---

**Du kan nå oss her**

Postboks 6562 ETTERSTAD, 0606 Oslo, Norge

Email: [kurs.ecs.no@arrow.com](mailto:kurs.ecs.no@arrow.com)

Phone: +47 22 02 81 00



# NetApp SnapCenter Administration

**CODE:**

NEP\_SNAP-C-ADM

**LENGTH:**

24 Hours (3 days)

**PRICE:**

kr28,950.00

## Description

This course focuses on the deployment of NetApp® SnapCenter® Server 4.4. You learn how to install, monitor, and manage SnapCenter Server. The course also discusses installation and use of licenses and role-based access control. You learn how to prepare hosts, install SnapCenter Plug-ins, and connect to NetApp ONTAP® AFF and FAS storage systems. You also review backup and restore of Windows file system data and the configuration of SnapMirror® and SnapVault® relationships for use with SnapCenter software. The course materials include an exercise workbook that serves as an on-the-job reference guide.

## Objectives

This course focuses on enabling you to do the following:

- Explain the benefits and relationships between the various components of the SnapCenter solution
- Describe the methods to install the SnapCenter Server software
- Perform SnapCenter configuration of role-based access control, installation of licenses, and connections to storage VMs (storage virtual machines, also known as SVMs)
- Configure hosts and SnapCenter Server Plug-in packages
- Prepare data protection relationships for SnapCenter software
- Perform backup and restore of Windows data
- Explain monitoring and managing capabilities of SnapCenter Server

## Audience

- NetApp and NetApp Partner Professional Services
- Systems Engineers
- NetApp Customers

## Prerequisites

The SnapCenter Fundamentals elearning training should be undertaken prior to this class. This is delivered free of charge via the NetApp Learning Center. Please contact us via the link below for any additional support..

## Contact Us

## Programme

### Module 1: SnapCenter Software Review

Introduction to the SnapCenter Suite

Server architecture

Plug-in Packages

licensing

Management Interfaces

Integration with ONTAP features

### Module 2: SnapCenter Server Deployment

Server Installation Workflow

Server Requirements

## Additional Installation Options

### Module 3: SnapCenter Server Configuration

License Management  
Server Connections to the Storage System  
Server RBAC

### Module 4: Preparing Hosts for SnapCenter

Add Hosts to the SnapCenter Server  
Installing Plug-in Packages

### Module 5: Assigning NetApp Storage to Windows Hosts

Configuring LUN storage on Windows  
Windows Disk Management  
Working with SMB Shares

### Module 6: Preparing Data Protection Relationships for SnapCenter

Data protection relationships with SnapCenter  
Preparing the storage systems for replication

### Module 7: Data Backup and Restore

Backup of Windows file systems  
Restore of Windows file systems  
Cloning Windows file system backups

### Module 8: Monitoring and Managing with the SnapCenter server

Managing the SnapCenter Repository  
Monitoring Activities  
Understanding SnapCenter Reporting Features

#### Labs:

Storage configuration  
SnapCenter server configuration  
Plug-in configuration, installation and monitoring  
Storage configuration  
SnapMirror and SnapVault configuration  
SnapCenter backup, restore and clone fundamentals  
Monitoring and managing SnapCenter software

## Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
13 Oct 2025	Virtual Classroom (GMT / UTC)	BST	English	Instructor Led Online		kr28,950.00

## Tilleggsinformasjon

[Denne treningen er også tilgjengelig som trening på stedet. Kontakt oss for å finne ut mer.](#)