



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00



Parallel Sysplex Implementation Workshop

CODE:	LENGTH:	PRICE:
ES42G	36 Hours (4.5 days)	kr40,475.00

Description

This course is developed for systems programmers working on an implementation of a Parallel Sysplex. It covers the details of z/OS and z/OS-related products and subsystems exploiting the Parallel Sysplex components. It is focused on the resource sharing side.

Objectives

- Understand the steps to implement a basic and full Parallel Sysplex
- Implement a basic sysplex
- Implement a multisystem base sysplex
- Implement the connectivity for a Parallel Sysplex
- Implement the features and functions of a Parallel Sysplex
- Implement the coupling facility key exploiters
- Understand the different recovery scenarios

Audience

This intermediate course should include system and subsystem programmers and personnel responsible for the implementation of the hardware and software for a Parallel Sysplex.

Prerequisites

Experience in the following areas is recommended:

- Installing **and** testing z/OS **and** related products
- HCD coding
- PARMLIB settings

Programme

Day 1

- Welcome
- Unit 1: Sysplex: Overview and definitions Lab 2: Building two stand-alone systems

Day 2

- Unit 2: Base sysplex definitions and commands
- Unit 3: Hardware Management Console Lab 3: Building a two system base sysplex

Day 3

- Unit 4: Base sysplex migration to Parallel Sysplex
- Unit 5: Coupling Facility architecture
- Lab 4: Base to Parallel Sysplex migration dynamically Lab 5: Dynamically add a third CF to sysplex

Day 4

- Lab 6: Implementation of CF exploiters

Day 5

- Unit 6: Sysplex operation and recovery
- Lab recovery

Options

Kursspråk svenska. Kursen kan komma att genomföras på engelska.

Session Dates

På begäran, [kontakta oss](#)

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)