



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00

CODE:	LENGTH:	PRICE:
JUN_JTNOOC	32 Hours (4 days)	kr28,500.00

Description

The course content is aimed at operators of devices running the Junos OS in a NOC environment. These operators include network engineers, administrators, support personnel, and reseller support personnel.

Objectives

After successfully completing this course, you should be able to:

- Reduce the time it takes to identify and isolate the root cause of an issue impacting your network.
- Gain familiarity with Junos products as they pertain to troubleshooting.
- Become familiar with online resources valuable to Junos troubleshooting.
- Gain familiarity with Junos tools used in troubleshooting.
- Identify and isolate hardware issues.
- Troubleshoot problems with the control plane.
- Troubleshoot problems with interfaces and other data plane components.
- Describe the staging and acceptance methodology.
- Troubleshoot routing protocols.
- Describe how to monitor your network with SNMP, RMON, JFlow, and port mirroring.
- Become familiar with JTAC procedures.

Prerequisites

JTNOOC is an introductory-level course. You should have basic networking knowledge and an understanding of the Open Systems Interconnection (OSI) reference model and the TCP/IP protocol suite and also attend the Introduction to the Junos Operating System (IJOS) course or have equivalent experience prior to attending this class.

Session Dates

På begäran, [kontakta oss](#)

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)