



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00

CODE:

NEP_OT-SANA 9.8

LENGTH:

16 Hours (2 days)

PRICE:

kr24,000.00

Description

In this course, you learn to configure NetApp® ONTAP® 9 data management software for a SAN environment. The course provides information about block-level protocols, including FC, FCoE, iSCSI, and NVMe, on Microsoft Windows Server and Linux host operating systems. Management of SAN storage provisioning, protocols, hosts, availability and data protection, and using best practices are also discussed.

An introduction to NVMe over Fibre Channel (NVMe/FC) is provided.

This course focuses on ONTAP 9 functionality and includes lecture and a hands-on exercise environment.

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
12 Dec 2024	Virtual Classroom (Timezone Stockholm)	CET	English	Instructor Led Online		kr24,000.00
17 Feb 2025	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr24,000.00
10 Apr 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr24,000.00
06 May 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr24,000.00
19 Jun 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr24,000.00
15 Sep 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr24,000.00
15 Dec 2025	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr24,000.00

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)