



Enterprise Computing Solutions - Education Services

## TRAINING OFFERING

---

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: [edu.ecs.se@arrow.com](mailto:edu.ecs.se@arrow.com)  
Phone: +46 8 555 188 00



# NetApp SnapCenter Administration

CODE:	LENGTH:	PRICE:
NEP_SNAP-C-ADM	24 Hours (3 days)	kr38,500.00

## Description

This course focuses on the deployment of NetApp® SnapCenter® Server 4.4. You learn how to install, monitor, and manage SnapCenter Server. The course also discusses installation and use of licenses and role-based access control. You learn how to prepare hosts, install SnapCenter Plug-ins, and connect to NetApp ONTAP® AFF and FAS storage systems. You also review backup and restore of Windows file system data and the configuration of SnapMirror® and SnapVault® relationships for use with SnapCenter software. The course materials include an exercise workbook that serves as an on-the-job reference guide.

## Objectives

This course focuses on enabling you to do the following:

- Explain the benefits and relationships between the various components of the SnapCenter solution
- Describe the methods to install the SnapCenter Server software
- Perform SnapCenter configuration of role-based access control, installation of licenses, and connections to storage VMs (storage virtual machines, also known as SVMs)
- Configure hosts and SnapCenter Server Plug-in packages
- Prepare data protection relationships for SnapCenter software
- Perform backup and restore of Windows data
- Explain monitoring and managing capabilities of SnapCenter Server

## Audience

- NetApp and NetApp Partner Professional Services
- Systems Engineers
- NetApp Customers

## Prerequisites

The SnapCenter Fundamentals elearning training should be undertaken prior to this class. This is delivered free of charge via the NetApp Learning Center. Please contact us via the link below for any additional support.

## Contact Us

## Programme

### Module 1: SnapCenter Software Review

Introduction to the SnapCenter Suite

Server architecture

Plug-in Packages

licensing

Management Interfaces

Integration with ONTAP features

### Module 2: SnapCenter Server Deployment

Server Installation Workflow

Server Requirements

## Additional Installation Options

### **Module 3: SnapCenter Server Configuration**

License Management

Server Connections to the Storage System

Server RBAC

### **Module 4: Preparing Hosts for SnapCenter**

Add Hosts to the SnapCenter Server

Installing Plug-in Packages

### **Module 5: Assigning NetApp Storage to Windows Hosts**

Configuring LUN storage on Windows

Windows Disk Management

Working with SMB Shares

### **Module 6: Preparing Data Protection Relationships for SnapCenter**

Data protection relationships with SnapCenter

Preparing the storage systems for replication

### **Module 7: Data Backup and Restore**

Backup of Windows file systems

Restore of Windows file systems

Cloning Windows file system backups

### **Module 8: Monitoring and Managing with the SnapCenter server**

Managing the SnapCenter Repository

Monitoring Activities

Understanding SnapCenter Reporting Features

#### **Labs:**

Storage configuration

SnapCenter server configuration

Plug-in configuration, installation and monitoring

Storage configuration

SnapMirror and SnapVault configuration

SnapCenter backup, restore and clone fundamentals

Monitoring and managing SnapCenter software

## Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
26 Jan 2026	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr35,600.00
05 May 2026	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr35,600.00
01 Sep 2026	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr35,600.00
02 Nov 2026	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr35,600.00

## Ytterligare information

Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.