



Arrow ECS Finland Oy - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS Finland Oy, Lars Sonckin kaari 16, 02600 Espoo, Finland

Email: education.ecs.fi@arrow.com

Phone: 0870 251 1000

CODE:	LENGTH:	PRICE:
NEP_OT-SANI 9.8	24 Hours (3 days)	€3,060.00

Description

In this course, you learn the installation process for NetApp® ONTAP® 9 data management software for a SAN environment. The course provides information about block-level protocols, including FC, FCoE, NVMe, and iSCSI, on Microsoft Windows Server, Linux, and VMware ESXi host operating systems. The learning is reinforced through hands-on guided exercises. The course materials include a workbook that serves as an on-the-job reference guide.

Objectives

- Define and describe SAN environments that use iSCSI, FC, FCoE, and NVMe protocols
- Examine FC switch fabric, LUN masking, and zoning
- Create and configure storage VMs (storage virtual machines, also known as SVMs) to use FC and iSCSI protocols
- Configure Microsoft Windows Server, Red Hat Enterprise Linux, and ONTAP systems for iSCSI connectivity
- Configure Microsoft Windows Server, Red Hat Enterprise Linux, and ONTAP systems for FC connectivity
- Create and access a LUN from a Windows Server and a Red Hat Enterprise Linux server

Audience

Professionals who implement SAN solutions that use NetApp storage systems

Prerequisites

- Certification as a NetApp Data Management Administrator
- Working knowledge of ONTAP 9 software and storage area networking
- Completion of the following courses:
 - ONTAP Cluster Fundamentals
 - ONTAP SAN Fundamentals
 - ONTAP Cluster Administration

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
13 May 2024	Virtual Classroom (CET / UTC +1)		English	Instructor Led Online		€3,060.00
10 Jun 2024	Virtual Classroom (CET / UTC +1)		English	Instructor Led Online		€3,060.00
09 Sep 2024	Virtual Classroom (CET / UTC +1)		English	Instructor Led Online		€3,060.00
09 Dec 2024	Virtual Classroom (CET / UTC +1)		English	Instructor Led Online		€3,060.00

Additional Information

This training is also available as onsite training. Please contact us to find out more.