



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS B.V., Kromme Schaft 5, 3991 AR Houten, The Netherlands

Email: education.ecs.nl@arrow.com

Phone: +31 20 582 6109



ONTAP SAN Administration 9.8

CODE:	LENGTH:	PRICE:
NEP_OT-SANA9.8	16 Hours (2 days)	€1,900.00

Description

In this course, you learn to configure NetApp® ONTAP® 9 data management software for a SAN environment. The course provides information about block-level protocols, including FC, FCoE, iSCSI, and NVMe, on Microsoft Windows Server and Linux host operating systems. Management of SAN storage provisioning, protocols, hosts, availability and data protection, and using best practices are also discussed.

An introduction to NVMe over Fibre Channel (NVMe/FC) is provided. This course focuses on ONTAP 9 functionality and includes lecture and a hands-on exercise environment.

Objectives

- Summarize SAN architecture
- Demonstrate SAN configuration and LUN provisioning
- Use iSCSI, FC, FCoE, and NVMe over Fibre Channel (NVMe/FC) features and recommendations
- Manage ONTAP availability strategies and data protection for LUNs
- Illustrate management concepts for SAN environments
- Explore Foreign LUN Import

Audience

SAN Storage Administrators

Prerequisites

A working knowledge of ONTAP 9 software and storage area networking in addition to the Cluster Fundamentals, SAN Fundamentals and SAN Implementation elearning available FOC via the NetApp Learning Center. Please contact us for further support as appropriate..

[Contact Us](#)

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
12 Sep 2024	Virtual Classroom (GMT / UTC)	BST	English	Instructor Led Online		€1,900.00
12 Dec 2024	Virtual Classroom (GMT / UTC)	GMT	English	Instructor Led Online		€1,900.00

Additional Information

[This training is also available as onsite training. Please contact us to find out more.](#)