



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00



Introduction to IBM Power Virtual Servers (PowerVS)

CODE: ZL1_QZC34D **LENGTH:** 5.04 Hours **PRICE:** Free

Description

This course covers IBM Power Virtual Server (PowerVS) fundamentals, initial configuration, networking, storage and data migration concepts and use cases, illustrating these concepts with demos on how to use IBM PowerVS for certain major workloads.

½

This course addresses topics for IT architects, specialists, developers, sellers, or anyone looking to implement and manage workloads in the IBM Power Systems Virtual Server (PowerVS) on IBM Cloud.

Objectives

- Describe the capabilities of IBM PowerVS ½
- Identify and describe the IBM PowerVS usage framework ½
- List the key terminologies and management entities ½
- Create and migrate virtual servers on IBM PowerVS

Audience

Enrollment is not restricted.

Programme

- Unit 1: Introduction ½
- Unit 2: Initial Configuration ½
- Unit 3: Network ½
- Unit 4: Data Migration ½
- Unit 5: Demos* Demo 1: Creating a Power Virtual Servers Service in IBM Cloud ½* Demo 2: Deploying AIX Virtual Servers ½* Demo 3: Deploying Linux Virtual Servers ½* Demo 4: Deploying IBM i Virtual Servers

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
27 Jul 2024			English	Web based Training		kr2,055.00

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)