



Enterprise Computing Solutions - Education Services

NABÍDKA ŠKOLENÍ

Prosím kontaktujte nás zde

Arrow ECS, a.s., 28. října 3390/111a, 702 00 Ostrava

Email: training.ecs.cz@arrow.com

Phone: +420 597 488 811



AZ-801T00: Configuring Windows Server Hybrid Advanced Services

Kód:	DÉLKA:	CENA:
MCS_AZ-801T00	32 Hours (4 DENNÍ)	Kč bez DPH 58,750.00

Description

Cíle

- Harden the security configuration of the Windows Server operating system environment.
- Enhance hybrid security using Azure Security Center, Azure Sentinel, and Windows Update Management.
- Apply security features to protect critical resources.
- Implement high availability and disaster recovery solutions.
- Implement recovery services in hybrid scenarios.
- Plan and implement hybrid and cloud-only migration, backup, and recovery scenarios.
- Perform upgrades and migration related to AD DS, and storage.
- Manage and monitor hybrid scenarios using WAC, Azure Arc, Azure Automation and Azure Monitor.
- Implement service monitoring and performance monitoring, and apply troubleshooting.

Určeno pro

This four-day course is intended for Windows Server Hybrid Administrators who have experience working with Windows Server and want to extend the capabilities of their on-premises environments by combining on-premises and hybrid technologies. Windows Server Hybrid Administrators who already implement and manage on-premises core technologies want to secure and protect their environments, migrate virtual and physical workloads to Azure laas, enable a highly available, fully redundant environment, and perform monitoring and troubleshooting.

Job role: Administrator Preparation for exam: AZ-801 Features: none

Vstupní znalosti

Before attending this course, students must have:

- Experience with managing Windows Server operating system and Windows Server workloads in on-premises scenarios, including AD DS, DNS, DFS, Hyper-V, and File and Storage Services
- Experience with common Windows Server management tools (implied in the first prerequisite).
- Basic knowledge of core Microsoft compute, storage, networking, and virtualization technologies (implied in the first prerequisite).
- Experience and an understanding of core networking technologies such as IP addressing, name resolution, and Dynamic Host Configuration Protocol (DHCP)
- Experience working with and an understanding of Microsoft Hyper-V and basic server virtualization concepts
- An awareness of basic security best practices
- Basic understanding of security-related technologies (firewalls, encryption, multi-factor authentication, SIEM/SOAR).
- Basic knowledge of on-premises resiliency Windows Server-based compute and storage technologies (Failover Clustering, Storage Spaces).
- Basic experience with implementing and managing IaaS services in Microsoft Azure Basic knowledge of Azure Active Directory
- Experience working hands-on with Windows client operating systems such as Windows 10 or Windows 11
- Basic experience with Windows PowerShell

An understanding of the following concepts as related to Windows Server technologies:

- High availability and disaster recovery
- Automation
- Monitoring
- Troubleshooting

After completing this module, students will be able to:

Implement highly available storage volumes by using Clustered Share Volumes.

Implement highly available Windows Server workloads using failover clustering.

Describe Hyper-V VMs load balancing.

Implement Hyper-V VMs live migration and Hyper-V VMs storage migration.

Describe Windows Server File Server high availability options.

Implement scaling for virtual machine scale sets and load-balanced VMs.

Implement Azure Site Recovery.

Module 4:

Disaster recovery in Windows Server

This module introduces Hyper-V Replica as a business continuity and disaster recovery solution for a virtual environment. The module discusses Hyper-V Replica scenarios and use cases, and prerequisites to use it. The module also discusses how to implement Azure Site Recovery in on-premises scenarios to recover from disasters.

Lessons

Implement Hyper-V Replica

Protect your on-premises infrastructure from disasters with Azure Site Recovery

Lab : Implementing Hyper-V Replica and Windows Server Backup

Implementing Hyper-V Replica

Implementing backup and restore with Windows Server Backup

After completing this module, students will be able to:

Describe Hyper-V Replica, pre-requisites for its use, and its high-level architecture and components

Describe Hyper-V Replica use cases and security considerations.

Configure Hyper-V Replica settings, health monitoring, and failover options.

Describe extended replication.

Replicate, failover, and failback virtual machines and physical servers with Azure Site Recovery.

Module 5:

Implementing recovery services in hybrid scenarios

This module covers tools and technologies for implementing disaster recovery in hybrid scenarios, whereas the previous module focus on BCDR solutions for on-premises scenarios. The module begins with Azure Backup as a service to protect files and folders before highlighting how to implement Recovery Vaults and Azure Backup Policies. The module describes how to recover Windows IaaS virtual machines, perform backup and restore of on-premises workloads, and manage Azure VM backups. The modules also covers how to provide disaster recovery for Azure infrastructure by managing and orchestrating replication, failover, and failback of Azure virtual machines with Azure Site Recovery.

Lessons

Implement hybrid backup and recovery with Windows Server IaaS

Protect your Azure infrastructure with Azure Site Recovery

Protect your virtual machines by using Azure Backup

Lab : Implementing Azure-based recovery services

Implementing the lab environment

Creating and configuring an Azure Site Recovery vault

Implementing Hyper-V VM protection by using Azure Site Recovery vault

Implementing Azure Backup

After completing this module, students will be able to:

Recover Windows Server IaaS virtual machines by using Azure Backup.

Use Azure Backup to help protect the data for on-premises servers and virtualized workloads.

Implement Recovery Vaults and Azure Backup policies.

Protect Azure VMs with Azure Site Recovery.

Run a disaster recovery drill to validate protection.

Failover and failback Azure virtual machines.

Module 6:

Upgrade and migrate in Windows Server

This module discusses approaches to migrating Windows Server workloads running in earlier versions of Windows Server to more current versions. The module covers the necessary strategies needed to move domain controllers to Windows Server 2022 and describes how the Active Directory Migration Tool can consolidate domains within a forest or migrate domains to a new AD DS forest. The module also discusses the use of Storage Migration Service to migrate files and file shares from existing file servers to new servers running Windows Server 2022. Finally, the module covers how to install and use the Windows Server Migration Tools cmdlets to migrate commonly used server roles from earlier versions of Windows Server.

Lessons

Active Directory Domain Services migration

Migrate file server workloads using Storage Migration Service

Migrate Windows Server roles

Lab : Migrating Windows Server workloads to IaaS VMs

Deploying AD DS domain controllers in Azure

Migrating file server shares by using Storage Migration Service

After completing this module, students will be able to:

Compare upgrading an AD DS forest and migrating to a new AD DS forest.

Describe the Active Directory Migration Tool (ADMT).

Identify the requirements and considerations for using Storage Migration Service.

Describe how to migrate a server with storage migration.

Use the Windows Server Migration Tools to migrate specific Windows Server roles.

Module 7:

Implementing migration in hybrid scenarios

This module discusses approaches to migrating workloads running in Windows Server to an infrastructure as a service (IaaS) virtual machine. The module introduces using Azure Migrate to assess and migrate on-premises Windows Server instances to Microsoft Azure. The module also covers how to migrate a workload running in Windows Server to an infrastructure as a service (IaaS) virtual machine (VM) and to Windows Server 2022 by using Windows Server migration tools or the Storage Migration Service. Finally, this module describes how to use the Azure Migrate App Containerization tool to containerize and migrate ASP.NET applications to Azure App Service.

Lessons

Migrate on-premises Windows Server instances to Azure IaaS virtual machines

Upgrade and migrate Windows Server IaaS virtual machines

Containerize and migrate ASP.NET applications to Azure App Service

Lab : Migrating on-premises VMs servers to IaaS VMs

Implementing assessment and discovery of Hyper-V VMs using Azure Migrate

Implementing migration of Hyper-V workloads using Azure Migrate

After completing this module, students will be able to:

Plan a migration strategy and choose the appropriate migration tools.

Perform server assessment and discovery using Azure Migrate.

Migrate Windows Server workloads to Azure VM workloads using Azure Migrate.

Explain how to migrate workloads using Windows Server Migration tools.

Migrate file servers by using the Storage Migration Service.

Discover and containerize ASP.NET applications running on Windows.

Migrate a containerized application to Azure App Service.

Module 8:

Server and performance monitoring in Windows Server

This module introduces a range of tools to monitor the operating system and applications on a Windows Server computer as well as describing how to configure a system to optimize efficiency and to troubleshoot problems. The module covers how Event Viewer provides a convenient and accessible location for observing events that occur, and how to interpret the data in the event log. The module also covers how to audit and diagnose a Windows Server environment for regulatory compliance, user activity, and troubleshooting. Finally, the module explains how to troubleshoot AD DS service failures or degraded performance, including recovery of deleted objects and the AD DS database, and how to troubleshoot hybrid authentication issues.

Lessons

Monitor Windows Server performance

Lab : Monitoring and troubleshooting Windows Server

Manage and monitor Windows Server event logs

Establishing a performance baseline

Implement Windows Server auditing and diagnostics

Identifying the source of a performance problem

Troubleshoot Active Directory

Viewing and configuring centralized event logs

After completing this module, students will be able to:

Explain the fundamentals of server performance tuning.

Use built-in tools in Windows Server to monitor server performance.

Use Server Manager and Windows Admin Center to review event logs.

Implement custom views.

Configure an event subscription.

Audit Windows Server events.

Configure Windows Server to record diagnostic information.

Recover the AD DS database and objects in AD DS.

Troubleshoot AD DS replication.

Troubleshoot hybrid authentication issues.

Module 9:

Implementing operational monitoring in hybrid scenarios

This module covers using monitoring and troubleshooting tools, processes, and best practices to streamline app performance and availability of Windows Server IaaS VMs and hybrid instances. The module describes how to implement Azure Monitor for IaaS VMs in Azure, implement Azure Monitor in on-premises environments, and use dependency maps. The module then explains how to enable diagnostics to get data about a VM, and how to view VM metrics in Azure Metrics Explorer, and how to create a metric alert to monitor VM performance. The module then covers how to monitor VM performance by using Azure Monitor VM Insights. The module then describes various aspects of troubleshooting on premises and hybrid network connectivity, including how to diagnose common issues with DHCP, name resolution, IP configuration, and routing. Finally, the module examines how to troubleshoot configuration issues that impact connectivity to Azure-hosted Windows Server virtual machines (VMs), as well as approaches to resolve issues with VM startup, extensions, performance, storage, and encryption.

Lessons

Monitor Windows Server IaaS Virtual Machines and hybrid instances

Monitor the health of your Azure virtual machines by using Azure Metrics Explorer and metric alerts

Monitor performance of virtual machines by using Azure Monitor VM Insights

Troubleshoot on-premises and hybrid networking

Troubleshoot Windows Server Virtual Machines in Azure

Lab : Monitoring and troubleshooting of IaaS VMs running Windows Server

Enabling Azure Monitor for virtual machines

Setting up a VM with boot diagnostics

Setting up a Log Analytics workspace and Azure Monitor VM Insights

After completing this module, students will be able to:

Implement Azure Monitor for IaaS VMs in Azure and in on-premises environments.

Implement Azure Monitor for IaaS VMs in Azure and in on-premises environments.

View VM metrics in Azure Metrics Explorer.

Use monitoring data to diagnose problems.

Evaluate Azure Monitor Logs and configure Azure Monitor VM Insights.

Configure a Log Analytics workspace.

Troubleshoot on-premises connectivity and hybrid network connectivity.

Troubleshoot AD DS service failures or degraded performance.

Recover deleted security objects and the AD DS database.

Troubleshoot hybrid authentication issues.

Termíny školení

Termíny školení na vyžádání, [kontaktujte nás prosím](#)

Dodatečné informace

Školení je možné zajistit na míru. [Kontaktujte nás pro bližší informace.](#)