



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS, Nidderdale House, Beckwith Knowle, Harrogate, HG3 1SA

Email: educationteam.ecs.uk@arrow.com
Phone: 0870 251 1000



Sterling Order Management System: Configuring Organizations, Participants, and User Security

CODE:	LENGTH:	PRICE:
6F140G	5.04 Hours	£290.00

Description

This course provides an overview of Applications Manager and Sterling Order Management System. It describes the business models supported by Sterling Order Management System. It also throws light on how to create organizations, define participants, create users, and configure user permissions. In this 5-hour long self-paced training interactive video course, students learn about topics such as how to map participants to different roles defined in Sterling Order Management System, configure attributes for the roles, configure prerequisites for user creation, and configure users and data access policies. The course involves procedural information, demonstrations, quizzes, and exercises in the form of hands-on labs and pen-and-paper activity, and their solutions. You must complete all of the required activities before you can take the quizzes. The course certificate is awarded after passing all the quizzes.

Objectives

After completing this course, you should be able to:

- Use the Application Manager
- List the Roles
- Map the participant details to their appropriate roles using the Application Platform.
- Create and assign different attributes for the participants.

Audience

Order Management developers and implementers.

Programme

- Introduction to Configuring Organizations
- Overview of Application Manager
- Defining Participants and Roles
- Configuring Organizations
- Assigning Attributes to Roles

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
23 Nov 2024			English	Self Paced Training		£290.00

Additional Information

This training is also available as onsite training. Please contact us to find out more.