



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

You can reach us at:

Arrow Enterprise Computing Solutions Ltd, Part 1st Floor, Suite 1D/1, Central House, Otley Road, Harrogate, HG3 1UG

Email: educationteam.ecs.uk@arrow.com
Phone: 0870 251 1000



ONTAP SAN Implementation

CODE:

NEP_OT-SANI

LENGTH:

24 Hours (3 days)

PRICE:

£2,660.00

Description

Learn how to install NetApp® ONTAP® 9 data management software for a SAN environment. Explore block-level protocols on Microsoft Windows Server and Linux host operating systems, including FC, FCoE, NVMe, and iSCSI. Apply your knowledge through hands-on guided exercises in a lab environment and through an exercise workbook that serves as an on-the-job reference guide.

Objectives

- Discuss SAN fundamentals for ONTAP software
- Explain ONTAP SAN resource provisioning
- Describe iSCSI, FC, and FCoE configuration in ONTAP software
- Explain the NVMe over Fabrics (NVMe-oF) implementation in ONTAP software
- Discuss host configuration requirements
- Explain Windows and Linux configuration for iSCSI
- Describe Windows and Linux configuration for FC

Audience

- Administrators
- Engineers
- Architects

Prerequisites

- Certification as a NetApp Data Management Administrator
- Working knowledge of ONTAP 9 software and storage area networking
- ONTAP Cluster Fundamentals via NetApp Learning Centre
- ONTAP SAN Fundamentals via NetApp Learning Centre
- ONTAP Cluster Administration via NetApp Learning Centre

Programme

Module 0: Introduction

- Classroom logistics
- Course prerequisites
- Course agenda

Module 1: ONTAP SAN fundamentals

- Implementing iSCSI, FCP, FCoE, and NVMe-oF SAN in ONTAP software
- SAN architecture
- Interoperability Matrix Tool
- SAN scalability and maximums

Module 2: ONTAP SAN resource provisioning

- IP SAN configurations
- FC SAN configurations
- LUN provisioning

Module 3: ONTAP iSCSI configuration concepts

- iSCSI configuration recommendations

- iSCSI feature overview
- iSCSI configuration workflow

Module 4: ONTAP FC configuration concepts

- FC configuration recommendations
- FC and FCoE zoning
- Cisco switches
- Brocade switches

Module 5: NVMe-oF configuration

- NVMe
- NVMe-oF
- NVMe integration into ONTAP software

Module 6: Host integration

- Host considerations
- Windows hosts
- Linux and UNIX hosts
- LUN offset

Module 7: Microsoft Windows IP SAN connectivity

- Configuring a Windows host for iSCSI
- iSCSI configuration

Module 8: Linux IP SAN connectivity

- Linux iSCSI configuration
- Linux iSCSI implementation

Module 9: Windows FC SAN connectivity

- Configuring a Windows host for FC
- Identifying the WWNN and WWPN on a Windows host
- Implementing and verifying multipath FC connectivity between a Windows host and ONTAP software

Module 10: Linux FC SAN connectivity

- Configuring a Linux host for FC
- Identifying WWNNs on a Linux host
- Implementing and verifying multipath FC connectivity between a Linux host and ONTAP software

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
13 Oct 2025	Virtual Classroom	BST	English	Instructor Led Online		£2,660.00
15 Dec 2025	Virtual Classroom	GMT	English	Instructor Led Online	Yes	£2,660.00 £2,128.00
28 Jan 2026	Virtual Classroom	GMT	English	Instructor Led Online		£2,660.00
05 May 2026	Virtual Classroom	BST	English	Instructor Led Online		£2,660.00
01 Sep 2026	Virtual Classroom	BST	English	Instructor Led Online		£2,660.00
04 Nov 2026	Virtual Classroom	GMT	English	Instructor Led Online		£2,660.00

Additional Information

[This training is also available as onsite training. Please contact us to find out more.](#)