



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS, Nidderdale House, Beckwith Knowle, Harrogate, HG3 1SA

Email: educationteam.ecs.uk@arrow.com
Phone: 0870 251 1000



InfoSphere MDM Workbench V11

CODE:	LENGTH:	PRICE:
-------	---------	--------

1Z840G	24 Hours	£600.00
--------	----------	---------

Description

This course is designed for anyone who wants to get an understanding of how to use and customize the InfoSphere Master Data Management using the InfoSphere MDM Workbench. This course takes a you through the process customizing both the Virtual and Physical MDM using the InfoSphere MDM Workbench. The focus of the course is on the core features of the Workbench: Creating a Physical MDM Addition, creating a Physical MDM Extension, creating a Physical MDM Behavior Extension, creating a composite service, deploying a Virtual MDM configuration, configuring the Virtual Data Model, creating a Virtual custom Composite View, creating a Virtual Callout Handler, generating an enterprise service interface using the Virtual data model and customizing a Hybrid implementation. For each core area, the instructor will explain the high-level concepts, have them work with the feature and then demo and review the feature details. Heavy emphasis is put on exercises and activities, allowing them to apply the knowledge that they learn in the classroom, after course conclusion.

If you are enrolling in a Self Paced Virtual Classroom or Web Based Training course, before you enroll, please review the **Self-Paced Virtual Classes and Web-Based Training Classes** on our Terms and Conditions page, as well as the system requirements, to ensure that your system meets the minimum requirements for this course.
<http://www.ibm.com/training/terms>

Objectives

- Understand the MDM Architecture and how the Physical, Virtual and Hybrid MDM handles a service request
- Understand the core Workbench features available for the InfoSphere MDM
- Understand how MDM using OSGi for deploying customizations to the product
- Create a new Physical MDM Entity using the Workbench Wizard
- Extend an existing Physical MDM Entity using the Workbench Wizard
- Extend an existing Physical MDM Service using the Workbench Wizard
- Create a new Composite Service using a transient object containing other existing business objects
- Customize and deploy a Virtual configuration
- Create a new Virtual Callout Handler
- Create a new Virtual Composite View
- Generate new Services based on the Virtual configuration (eSOA)
- Customize a Hybrid MDM implementation
- Understand the Adaptive Service Interface (ASI)

Audience

This advanced course is for Infrastructure Specialist, Senior Technical Specialist, Technical Specialist, Support Engineers, System Architects.

Prerequisites

You should have attended:

- Data Model and Service Mapping for the InfoSphere MDM Advanced Edition V10 (ZZ610)

It is also recommended that you have working knowledge of Java development and XML concepts as it will be used during the exercises.

Programme

IntroductionInfoSphere MDM Architecture

- Virtual, Physical and Hybrid MDM
- Request/Response Framework
- Core Physical MDM
- Core Virtual MDM

OSGi and MDMPPhysical MDM Data Additions

- Additions Architecture
- Creating an MDM Module Project
- Creating an Addition
- Core Property Files
- Custom Code Tables

Physical MDM Data Extensions

- Extensions Architecture
- Creating an Extension

Physical MDM Behavior Extensions

- Behavior Extensions Architecture
- Creating an Behavior Extension

Composite Services

- XML Composite Services
- Java (Business Proxy) Composite Services

Adaptive Service Interface (ASI)

- How ASI fits into the InfoSphere MDM Architecture
- How to build an new Service Mapping
- How to tailor service for your organization

Virtual Data Model

- Virtual data model
- Creating a new MDM Virtual Attribute Type
- Deploying the Virtual Configuration

Virtual Handlers

- Callout Handlers
- Event Handlers
- Composite View Handlers

eSOA Toolkit

- Understand the eSOA Toolkit
- Generate java and WebService client

Hybrid MDM

- Hybrid MDM assets
- Hybrid MDM service flow
- Hybrid MDM Customizations

AGENDA:Day 1

- Unit 1: InfoSphere MDM Architecture
- Unit 2: OSGi and MDM

Physical MDM

- Unit 3: Data Additions
 - Exercise 1: Additions
- Unit 4: Physical Data Extensions
 - Exercise 2: Extensions – New Person Attribute

Day 2

- Unit 5: MDM Physical Behavior Extensions
 - Exercise 3: Behavior Extension
- Unit 6: Composite Services
 - Exercise 4: Composite Services
- Unit 7: Adaptive Services Interface (ASI)

Virtual MDM

- Unit 8: Virtual Data Model
 - Exercise 5: Creating a Custom Attribute Type

Day 3

- Unit 9: Virtual Handlers
 - Exercise 6: Callout Handler
 - Exercise 7: Custom Composite View
- Unit 10: eSOA Toolkit
 - Exercise 8: eSOAToolkig
- Unit 11: Hybrid MDM
 - Exercise 9: Hybrid Customization

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
27 Jul 2024			English	Web based Training		£600.00

Additional Information

[This training is also available as onsite training. Please contact us to find out more.](#)