



## TRAINING OFFERING

---

**You can reach us at:**

Arrow ECS, Nidderdale House, Beckwith Knowle, Harrogate, HG3 1SA

Email: [educationteam.ecs.uk@arrow.com](mailto:educationteam.ecs.uk@arrow.com)

Phone: 0870 251 1000



# z/OS JES2 Operator Training

CODE:	LENGTH:	PRICE:
ES28G	20 Hours (2.5 days)	£1,950.00

## Description

This course is designed to give the z/OS Operator personnel as well as entry systems programmers an overview about JES2. The students should be able to use JES2 commands at the z/OS Console and use SDSF.

## Objectives

- Understand the z/OS environment and JES2 role
- Start JES2 with focus on options and shutdown
- Control JES2 with commands and SDSF
- Control JES2 job flow, selection, and processing
- Control output processing and printers
- Understand z/OS influence on JES2 processing

## Audience

This intermediate course is for z/OS Operators (console and periphery), help desk, and support personnel.

## Training Development

Roadmaps that reference this course are:

- [z/OS Operation and Parallel Sysplex](#)
- [z/OS Operation and Parallel Sysplex](#)

## Prerequisites

You should have completed:

- z/OS Basic System Skill (ES10)
- z/OS System Operations (ES27)

## Programme

### Day 1

- Welcome
- Unit 1 - z/OS and JES2 overview
- Unit 1 - SDSF demo
- Unit 2 - Manage a JES2 subsystem
- Exercise 1 - Start a z/OS system

### Day 2

- Review day 1
- Exercise 1 - Start a z/OS system (continued)
- Exercise 2 - Log on to TSO

- Unit 3 - Control JES2
- Exercise 3 - JES2 commands
- Unit 4 - Checkpoint, Spool offload, printer server, NJE, RJE, and MAS

### **Day 3**

- Review day 2
- Unit 4 - Checkpoint, Spool offload, printer server, NJE, RJE, and MAS (continued)
- Exercise 4 - Spool and checkpoint management
- Exercise 5 - System display and search facility
- Exercise 6 - Automatic Command Facility (optional)

### **Session Dates**

On request. Please [Contact Us](#)

### **Additional Information**

[This training is also available as onsite training. Please contact us to find out more.](#)