



TRAINING OFFERING

You can reach us at:

Arrow ECS, Nidderdale House, Beckwith Knowle, Harrogate, HG3 1SA

Email: educationteam.ecs.uk@arrow.com

Phone: 0870 251 1000



AZ-800T00: Administering Windows Server Hybrid Core Infrastructure

CODE:	LENGTH:	PRICE:
MCS_AZ-800T00	32 Hours (4 days)	£2,295.00

Description

This course teaches IT Professionals how to manage core Windows Server workloads and services using on-premises, hybrid, and cloud technologies. The course teaches IT Professionals how to implement and manage on-premises and hybrid solutions such as identity, management, compute, networking, and storage in a Windows Server hybrid environment.

Audience

This four-day course is intended for Windows Server Hybrid Administrators who have experience working with Windows Server and want to extend the capabilities of their on-premises environments by combining on-premises and hybrid technologies. Windows Server Hybrid Administrators implement and manage on-premises and hybrid solutions such as identity, management, compute, networking, and storage in a Windows Server hybrid environment.

Prerequisites

Before attending this course, students must have:

Experience with managing Windows Server operating system and Windows Server workloads in on-premises scenarios, including AD DS, DNS, DFS, Hyper-V, and File and Storage Services

Experience with common Windows Server management tools (implied in the first prerequisite).

Basic knowledge of core Microsoft compute, storage, networking, and virtualization technologies (implied in the first prerequisite).

Experience and an understanding of core networking technologies such as IP addressing, name resolution, and Dynamic Host Configuration Protocol (DHCP)

Experience working with and an understanding of Microsoft Hyper-V and basic server virtualization concepts

Basic experience with implementing and managing IaaS services in Microsoft Azure Basic knowledge of Azure Active Directory

Experience working hands-on with Windows client operating systems such as Windows 10 or Windows 11

Basic experience with Windows PowerShell

Programme

Module 1: Identity services in Windows Server

This module introduces identity services and describes Active Directory Domain Services (AD DS) in a Windows Server environment. The module describes how to deploy domain controllers in AD DS, as well as Azure Active Directory (AD) and the benefits of integrating Azure AD with AD DS. The module also covers Group Policy basics and how to configure group policy objects (GPOs) in a domain environment.

Lessons

Introduction to AD DS Manage AD DS domain controllers and FSMO roles Implement Group Policy Objects

Lab : Implementing identity services and Group Policy

Deploying a new domain controller on Server Core

Configuring Group Policy

Manage advanced features of AD DS After completing this module, students will be able to:

Describe AD DS in a Windows Server environment. Deploy domain controllers in AD DS.

Describe Azure AD and benefits of integrating Azure AD with AD DS.

Explain Group Policy basics and configure GPOs in a domain environment.

Module 2: Implementing identity in hybrid scenarios

This module discusses how to configure an Azure environment so that Windows IaaS workloads requiring Active Directory are supported. The module also covers integration of on-premises Active Directory Domain Services (AD DS) environment into Azure. Finally, the module explains how to extend an existing Active Directory environment into Azure by placing IaaS VMs configured as domain controllers onto a specially configured Azure virtual network (VNet) subnet.

Lessons

Implement hybrid identity with Windows Server Deploy and manage Azure IaaS Active Directory domain controllers in Azure

Lab : Implementing integration between AD DS and Azure AD

Preparing Azure AD for AD DS integration

Preparing on-premises AD DS for Azure AD integration

Downloading, installing, and configuring Azure AD Connect

Verifying integration between AD DS and Azure AD

Implementing Azure AD integration features in AD DS

After completing this module, students will be able to:

Integrate on-premises Active Directory Domain Services (AD DS) environment into Azure.

Install and configure directory synchronization using Azure AD Connect. Implement and configure Azure AD DS.

Implement Seamless Single Sign-on (SSO). Implement and configure Azure AD DS. Install a new AD DS forest on an Azure VNet.

Module 3: Windows Server administration

This module describes how to implement the principle of least privilege through Privileged Access Workstation (PAW) and Just Enough Administration (JEA). The module also highlights several common Windows Server administration tools, such as Windows Admin Center, Server Manager, and PowerShell. This module also describes the post-installation configuration process and tools available to use for this process, such as sconfig and Desired State Configuration (DSC).

Lessons

Perform Windows Server secure administration Describe Windows Server administration tools

Perform post-installation configuration of Windows Server Just Enough Administration in Windows Server

Lab : Managing Windows Server

Implementing and using remote server administration

After completing this module, students will be able to: Explain least privilege administrative models.

Decide when to use privileged access workstations.

Select the most appropriate Windows Server administration tool for a given situation.

Apply different methods to perform post-installation configuration of Windows Server.

Constrain privileged administrative operations by using Just Enough Administration (JEA).

Module 4: Facilitating hybrid management

This module covers tools that facilitate managing Windows IaaS VMs remotely. The module also covers how to use Azure Arc with on-premises server instances, how to deploy Azure policies with Azure Arc, and how to use role-based access control (RBAC) to restrict access to Log Analytics data.

Lessons

Administer and manage Windows Server IaaS virtual machines remotely Manage hybrid workloads with Azure Arc

Lab : Using Windows Admin Center in hybrid scenarios

Provisioning Azure VMs running Windows Server

Implementing hybrid connectivity by using the Azure Network Adapter

Deploying Windows Admin Center gateway in Azure

Verifying functionality of the Windows Admin Center gateway in Azure

After completing this module, students will be able to:

Select appropriate tools and techniques to manage Windows IaaS VMs remotely.

Explain how to onboard on-premises Windows Server instances in Azure Arc.

Connect hybrid machines to Azure from the Azure portal. Use Azure Arc to manage devices. Restrict access using RBAC.

Module 5: Hyper-V virtualization in Windows Server

This module describes how to implement and configure Hyper-V VMs and containers. The module covers key features of Hyper-V in Windows Server, describes VM settings, and how to configure VMs in Hyper-V. The module also covers security technologies used with virtualization, such as shielded VMs, Host Guardian Service, admin-trusted and TPM-trusted attestation, and Key Protection Service (KPS). Finally, this module covers how to run containers and container workloads, and how to orchestrate container workloads on Windows Server using Kubernetes.

Lessons

Configure and manage Hyper-V Configure and manage Hyper-V virtual machines Secure Hyper-V workloads

Run containers on Windows Server Orchestrate containers on Windows Server using Kubernetes

Lab : Implementing and configuring virtualization in Windows Server

Creating and configuring VMs

Installing and configuring containers

After completing this module, students will be able to:

Install and configure Hyper-V on Windows Server.

Configure and manage Hyper-V virtual machines. Use Host Guardian Service to protect virtual machines.

Create and deploy shielded virtual machines. Configure and manage container workloads.

Orchestrate container workloads using a Kubernetes cluster.

Module 6: Deploying and configuring Azure VMs

This module describes Azure compute and storage in relation to Azure VMs, and how to deploy Azure VMs by using the Azure portal, Azure CLI, or templates. The module also explains how to create new VMs from generalized images and use Azure Image Builder templates to create and manage images in Azure. Finally, this module describes how to deploy Desired State Configuration (DSC) extensions, implement those extensions to remediate noncompliant servers, and use custom script extensions.

Lessons

Plan and deploy Windows Server IaaS virtual machines Customize Windows Server IaaS virtual machine images

Automate the configuration of Windows Server IaaS virtual machines

Lab : Deploying and configuring Windows Server on Azure VMs

Authoring Azure Resource Manager (ARM) templates for Azure VM deployment

Modifying ARM templates to include VM extension-based configuration

Deploying Azure VMs running Windows Server by using ARM templates

Configuring administrative access to Azure VMs running Windows Server

Configuring Windows Server security in Azure VMs

After completing this module, students will be able to:

Create a VM from the Azure portal and from Azure Cloud Shell. Deploy Azure VMs by using templates.

Automate the configuration of Windows Server IaaS VMs. Detect and remediate noncompliant servers.

Create new VMs from generalized images. Use Azure Image Builder templates to create and manage images in Azure.

Module 7: Network infrastructure services in Windows Server

This module describes how to implement core network infrastructure services in Windows Server, such as DHCP and DNS. This module also covers how to implement IP address management and how to use Remote Access Services.

Lessons

Deploy and manage DHCP Implement Windows Server DNS Implement IP address management Implement remote access

Lab : Implementing and configuring network infrastructure services in Windows Server

Deploying and configuring DHCP

Deploying and configuring DNS

After completing this module, students will be able to:

Implement automatic IP configuration with DHCP in Windows Server.

Deploy and configure name resolution with Windows Server DNS.

Implement IPAM to manage an organization's DHCP and DNS servers, and IP address space.

Select, use, and manage remote access components.

Implement Web Application Proxy (WAP) as a reverse proxy for internal web applications.

Module 8: Implementing hybrid networking infrastructure

This module describes how to connect an on-premises environment to Azure and how to configure DNS for Windows Server IaaS virtual machines. The module covers how to choose the appropriate DNS solution for your organization's needs, and run a DNS server in a Windows Server Azure IaaS VM. Finally, this module covers how to manage Microsoft Azure virtual networks (VNETs) and IP address configuration for Windows Server infrastructure as a service (IaaS) virtual machines.

Lessons

Implement hybrid network infrastructure Implement DNS for Windows Server IaaS VMs

Lab : Implementing Windows Server IaaS VM networking

Implementing virtual network routing in Azure

Implementing DNS name resolution in Azure

Implement Windows Server IaaS VM IP addressing and routing After completing this module, students will be able to:

Implement an Azure virtual private network (VPN). Configure DNS for Windows Server IaaS VMs.

Run a DNS server in a Windows Server Azure IaaS VM. Create a route-based VPN gateway using the Azure portal.

Implement Azure ExpressRoute. Implement an Azure wide area network (WAN). Manage Microsoft Azure virtual networks (VNETs).

Manage IP address configuration for Windows Server IaaS virtual machines (VMs).

Module 9: File servers and storage management in Windows Server

This module covers the core functionality and use cases of file server and storage management technologies in Windows Server.

The module discusses how to configure and manage the Windows File Server role, and how to use Storage Spaces and Storage Spaces Direct.

This module also covers replication of volumes between servers or clusters using Storage Replica.

Lessons

Manage Windows Server file servers Implement Storage Spaces and Storage Spaces Direct

Implement Windows Server Data Deduplication Implement Windows Server iSCSI Implement Windows Server Storage Replica

Lab : Implementing storage solutions in Windows Server

Implementing Data Deduplication

Configuring iSCSI storage

Configuring redundant Storage Spaces

Implementing Storage Spaces Direct

After completing this module, students will be able to: Configure and manage the Windows Server File Server role.

Protect data from drive failures using Storage Spaces.

Increase scalability and performance of storage management using Storage Spaces Direct.

Optimize disk utilization using Data DeDuplication. Configure high availability for iSCSI.

Enable replication of volumes between clusters using Storage Replica.

Use Storage Replica to provide resiliency for data hosted on Windows Servers volumes.

Module 10: Implementing a hybrid file server infrastructure

This module introduces Azure file services and how to configure connectivity to Azure Files. The module also covers how to deploy and implement Azure File Sync to cache Azure file shares on an on-premises Windows Server file server. This module also describes how to manage cloud tiering and how to migrate from DFSR to Azure File Sync.

Lab : Implementing Azure File Sync

Implementing DFS Replication in your on-premises environment

Creating and configuring a sync group

Replacing DFS Replication with File Sync–based replication

Verifying replication and enabling cloud tiering

Troubleshooting replication issues

Lessons

Overview of Azure file services Implementing Azure File Sync After completing this module, students will be able to:

Configure Azure file services. Configure connectivity to Azure file services. Implement Azure File Sync. Deploy Azure File Sync

Manage cloud tiering. Migrate from DFSR to Azure File Sync.

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
29 Jul 2024	Virtual Classroom	BST	English	Instructor Led Online		£2,295.00
18 Nov 2024	Virtual Classroom	GMT	English	Instructor Led Online		£2,295.00

Additional Information

[This training is also available as onsite training. Please contact us to find out more.](#)