



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

You can reach us at:

Arrow ECS B.V., Kromme Schaft 5, 3991 AR Houten, The Netherlands

Email: education.ecs.nl@arrow.com

Phone: +31 20 582 6109

CODE:	LENGTH:	PRICE:
FTN_FT-FWF	16 Hours (2 days)	€2,115.00

Description

In this course, you will learn how to deploy, configure, and troubleshoot secure wireless LAN using an integrated wireless solution. Using interactive labs, you will enforce your knowledge of deploying a secure wireless LAN centrally managed from the FortiGate wireless controller.

Objectives

After completing this course, you will be able to:

- Explore FortiPresence, FortiPlanner, and FortiAP Cloud
- Deploy a wireless network using the FortiGate integrated wireless controller
- Learn about different SSIDs traffic modes
- Deploy multiple wireless SSIDs
- Offer secure wireless access with 802.1x authentication
- Deploy wireless networks with VLANs
- Thwart hotspot hackers and rogue APs
- Understand fast roaming and wireless client load balancing
- Troubleshoot signal loss, slow connection, and authentication issues

Audience

This course is intended for networking and security professionals involved in the management, configuration, administration, and monitoring of the Fortinet integrated and/or cloud wireless solution.

Programme

1. Introduction to FortiOS Integrated Wireless
2. Wireless Controller
3. Access Point Profile
4. Advanced Configuration
5. Troubleshooting

Further Information

System Requirements If you take the online format of this class, you must use a computer that has the following:

- A high-speed internet connection
- An up-to-date web browser
- A PDF viewer
- Speakers or headphones
- HTML 5 support

You should use a wired Ethernet connection, not a WiFi connection. Firewalls, including Windows Firewall or FortiClient, must allow connections to the online labs.

Session Dates

On request. Please [contact us](#)

Additional Information

[This training is also available as onsite training. Please contact us to find out more.](#)