



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss her

Postboks 6562 ETTERSTAD, 0606 Oslo, Norge

Email: kurs.ecs.no@arrow.com

Phone: +47 22 02 81 00



CISSP Online Self-Paced Training

CODE:	LENGTH:	PRICE:
ISC_CISSP_OLSP	720 Hours	Request Price

Description

Official ISC2 Online Self-Paced CISSP Training is a groundbreaking way to prep for certification that uses artificial intelligence to customize your learning journey. It pinpoints areas that require additional focus and guides you through your exam prep in a way that's truly personalized.

Study smarter, not harder, with these key advantages:

- Personalized instruction
 - Content, pace and difficulty adapt to your individual knowledge, learning speed and confidence level.
- Enhanced engagement
 - Immediate feedback and dynamic content enable you to learn at an appropriate level.
- Time savings
 - Training time is optimized by focusing on areas that require the most review.
- Improved learning outcomes
 - The platform identifies areas requiring further review and provides targeted support to maximize your understanding of the content.

What's included with each option*:

- Self-paced online adaptive learning journey
- Data-driven analytics dashboard for real-time feedback on learner progress
- Robust search functionality to narrow topics
- Pre- and post-course assessments
- Knowledge checks and end-of-domain quizzes
- Official ISC2 CISSP eTextbook
- Official ISC2 CISSP Study Questions eBook
- Interactive content
- Domain-by-domain study sheets with key points
- Email content support
- Online interactive flash cards
- Glossary of Terms
- 24/7/365 chat technical support

*Learners receive same-day access to the course materials. Your 90- or 180-day access starts at date of purchase.

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
01 Jan 0001			English	Self Paced Training		Free

Tilleggsinformasjon

Denne treningen er også tilgjengelig som trening på stedet. Kontakt oss for å finne ut mer.