



Enterprise Computing Solutions - Education Services

## TRAINING OFFERING

---

**Du kan nå oss her**

Postboks 6562 ETTERSTAD, 0606 Oslo, Norge

Email: [kurs.ecs.no@arrow.com](mailto:kurs.ecs.no@arrow.com)

Phone: +47 22 02 81 00



## IMS Security

<b>CODE:</b>	<b>LENGTH:</b>	<b>PRICE:</b>
CM43G	32 Hours (4 days)	kr31,540.00

### Description

Learn implementation for Information Management System (IMS) using Resource Access Control Facility (RACF) as the external security manager, and the installation provided security exit routines. Apply classroom lectures with security paper lab exercises in which you setup the security definitions.

### Objectives

- Identify the IMS resources that must be protected
- Identify the types of security facilities available for each resource
- Develop a plan to implement security on your IMS systems
- Identify the tasks required in IMS and RACF to implement security
- Implement security for each resource using an appropriate security facility
- Code the security definitions in IMS and RACF to protect transactions, commands, data, dependent regions, Program Specification Blocks (PSB), terminals and other resources

### Audience

This is an intermediate course for security and IMS support individuals who design, implement, or administer security for IMS systems.

### Prerequisites

You should be familiar with RACF or IMS.

### Programme

- Introduction to IMS Security
- IMS Security Facilities
- IMS Security Options
- Introduction to RACF
- User ID and Sign On Verification
- Securing the IMS Control Region
- IMS Transaction Security
- IMS Command Security
- Security for Time Controlled Operations
- IMS Resource Access Security (RAS)
- IMS Database Security
- IMS Data Set Security
- Common Service Layer Security
- Security in an IMS Database Control Environment
- IMS and DB2 Security

### Session Dates

Ved forespørsel. Vennligst [kontakt oss](#)

## **Tilleggsinformasjon**

Denne treningen er også tilgjengelig som trening på stedet. [Kontakt oss](#) for å finne ut mer.