



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss her

Postboks 6562 ETTERSTAD, 0606 Oslo, Norge

Email: kurs.ecs.no@arrow.com

Phone: +47 22 02 81 00



CGRC Online Self-Paced Training

CODE:	LENGTH:	PRICE:
ISC_CGRC_OLSP	720 Hours	Request Price

Description

Official ISC2 Online Self-Paced CGRC Training is a groundbreaking way to prep for certification that uses artificial intelligence to customize your learning journey. It pinpoints areas that require additional focus and guides you through your exam prep in a way that's truly personalized.

Study smarter, not harder, with these key advantages:

- Personalized instruction
 - Content, pace and difficulty adapt to your individual knowledge, learning speed and confidence level.
- Enhanced engagement
 - Immediate feedback and dynamic content enable you to learn at an appropriate level.
- Time savings
 - Training time is optimized by focusing on areas that require the most review.
- Improved learning outcomes
 - The platform identifies areas requiring further review and provides targeted support to maximize your understanding of the content.

What's included with each option*:

- Self-paced online adaptive learning journey
- Data-driven analytics dashboard for real-time feedback on learner progress
- Robust search functionality to narrow topics
- Pre- and post-course assessments
- Knowledge checks and end-of-domain quizzes
- Official ISC2 CGRC eTextbook
- Official ISC2 CGRC Study Questions eBook
- Interactive content
- Domain-by-domain study sheets with key points
- Email content support
- Online interactive flash cards
- Glossary of Terms
- 24/7/365 chat technical support

*Learners receive same-day access to the course materials. Your 90- or 180-day access starts at date of purchase.

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
01 Jan 0001			English	Self Paced Training		Free

Tilleggsinformasjon

[Denne treningen er også tilgjengelig som trening på stedet. Kontakt oss for å finne ut mer.](#)