



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00



Horizon Deploy and Manage

CODE:

OMN_HDM88

LENGTH:

40 Hours (5 days)

PRICE:

kr54,500.00

Description

This five-day course gives you the hands-on skills to deliver virtual desktops and applications through a single virtual desktop infrastructure platform. You build on your skills in configuring and managing Horizon® 8 through a combination of lecture and hands-on labs. You learn how to configure and deploy pools of virtual machines and how to provide a customized desktop environment to end-users. Additionally, you learn how to install and configure a virtual desktop infrastructure platform. You learn how to install and configure Horizon® Connection Server™ Unified Access Gateway™ how to configure a load balancer for use with Horizon, and how to establish Cloud Pod Architecture.

Objectives

- By the end of this session, attendees should be able to:
- Recognize the features and benefits of Horizon
 - Use vSphere to create VMs to be used as desktops for Horizon
 - Create and optimize Windows VMs to create Horizon desktops
 - Install and Configure Horizon Agent on a Horizon desktop
 - Configure, manage, and entitle desktop pools of full VMs
 - Configure and manage the Horizon Client systems and connect the client to a Horizon desktop
 - Configure, manage, and entitle pools of instant-clone desktops
 - Create and use Remote Desktop Services (RDS) desktops and application pools
 - Monitor the Horizon environment using the Horizon Console Dashboard and Horizon Help Desk Tool
 - Identify Horizon Connection Server installation, architecture, and requirements
 - Describe the authentication and certificate options for the Horizon environment
 - Recognize the integration process and benefits of Omnissa® Access™ and Horizon 8
 - Compare the remote display protocols that are available in Horizon
 - Describe the 3D rendering options available in Horizon 8
 - Discuss scalability options available in Horizon 8
 - Describe different security options for the Horizon environment.

Audience

- Tier 1 Operators, administrators, and architects, responsible for the creation, maintenance, and or delivery of remote and virtual desktop services
- Additional duties can include the implementation, support, and administration of an organization's end-user computing infrastructure.

Prerequisites

- Before attending this course, you must have the following skills:
- Use vSphere Web Client
 - Create snapshots of virtual machines
 - Configure guest customization specifications
 - Modify virtual machine properties
 - Convert a virtual machine to a template
 - Microsoft Windows system administration experience:
 - Configure Active Directory services, including DNS, DHCP, and time synchronization
 - Restrict user activities by implementing Group Policy Objects
 - Configure Windows systems to enable Remote Desktop Connections

Programme

- 1 Course Introduction** • Introductions and course logistics • Course objectives
- 2 Introduction to Horizon**
- Recognize the features and benefits of Horizon
 - Describe the conceptual and logical architecture of Horizon
- 3 vSphere for Horizon** • Explain basic virtualization concepts
- Use vSphere Client™ to access your vCenter Server system and ESXi hosts
 - Create, provision, and remove a virtual machine
- 4 Create Windows Desktops** • Outline the steps to install Horizon Agent on Windows virtual machines
- Install Horizon Agent on a Windows virtual Machine
 - Optimize and prepare Windows virtual machines to set up Horizon desktop VMs
- 5 Create Linux Desktops**

- Create a Linux VM for Horizon • Install Horizon Agent on a Linux virtual machine
- Optimize and prepare Linux virtual machines to set up Horizon desktop VMs **6 Creating and Managing Desktop Pools**
- Identify the steps to set up a template for desktop pool deployment
- List the steps to add desktops to the Horizon® Connection Server™ inventory
- Compare dedicated-assignment and floating-assignment pools • Outline the steps to create an automated pool
- Define user entitlement • Explain the hierarchy of global, pool-level, and user-level policies **7 Horizon Client Options**
- Describe the different clients and their benefits • Access Horizon desktop using various Horizon clients and HTML
- Configure integrated printing, USB redirection, and the shared folders option
- Configure session collaboration and media optimization for Microsoft Teams **8 Creating and Managing Instant-Clone Desktops**
- List the advantages of instant clones • Explain the provisioning technology used for instant clone desktop pools
- Set up an automated pool of instant clones • Push updated images to instant clone desktop pools
- 9 Creating RDS Desktop and Application Pools** • Explain the difference between an RDS desktop pool and an automated pool
- Compare and contrast an RDS session host pool, a farm, and an application pool
- Create an RDS desktop pool and an application pool • Access RDS desktops and application from Horizon Client
- Use the instant clone technology to automate the build-out of RDSH farms • Configure load-balancing for RDSHs on a farm
- 10 Monitoring Horizon** • Monitor the status of the Horizon components using the Horizon Administrator console dashboard
- Monitor desktop sessions using the HelpDesk tool
- Monitor the performance of the remote desktop using the Horizon Performance Tracker **11 Horizon Connection Server**
- Recognize Horizon reference architecture • Identify the Horizon Connection Server supported features
- Identify the recommended system requirements for Horizon Connection Server • Configure Horizon event database
- Outline the steps for the initial configuration of Horizon Connection Server
- Discuss the AD LDS database as a critical component of Horizon Connection Server installation **12 Horizon Protocols**
- Compare the remote display protocols that are available in Horizon • Describe BLAST • Summarize BLAST Codec options
- List ideal applications for each BLAST codec • Describe BLAST and PCoIP ADMX GPO common configurations
- 13 Graphics in Horizon** • Describe the 3D rendering options available in Horizon 8 • Compare vSGA and vDGA
- List the steps to configure graphics cards for use in a Horizon environment **14 Securing Connections: Network**
- Compare tunnels and direct connections for client access to desktops • Discuss the benefits of using Unified Access Gateway
- List the Unified Access Gateway firewall rules • Configure TLS certificates in Horizon
- 15 Securing Connections: Authentication** • Compare the authentication options that Horizon Connection Server supports
- Restrict access to the Horizon remote desktops using restricted entitlements
- Describe the smart card authentication methods that Horizon Connection Server supports
- Explain the purpose of permissions, roles, and privileges in Horizon • Create custom roles **16 Horizon Scalability**
- Describe the purpose of a replica connection server
- Explain how multiple Horizon Connection Server instances in a pod maintain synchronization
- List the steps to configure graphics cards for use in a Horizon environment
- Configure a load balancer for use in a Horizon environment • Explain Horizon Cloud Pod Architecture LDAP replication and VIPA
- Explain Horizon Cloud Pod Architecture scalability options **17 Horizon Cloud and Universal Broker**
- Recognize the features and benefits of Horizon Cloud Service • Use Universal broker to connect to a Horizon Cloud instance
- Configure and pair the Horizon Cloud Connector appliance with Horizon Connection Server
- 18 Omnisia Access and Virtual Application Management** • Recognize the features and benefits of Workspace ONE Access
- Recognize the Workspace ONE Access console features • Explain identity management in Workspace ONE Access
- Explain access management in Workspace ONE Access • Describe the Workspace ONE Access directory integration
- Deploy virtual applications with Workspace services

Test and Certification

- Omnisia Certified Professional Desktop (OCPD)

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
08 Sep 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr54,500.00
29 Sep 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr54,500.00
13 Oct 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr54,500.00
27 Oct 2025	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr54,500.00
08 Dec 2025	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr54,500.00

Ytterligare information

Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.