



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00

CODE:	LENGTH:	PRICE:
NEP_OT-SANF	8 Hours (1 day)	kr12,500.00

Description

Learn how to administer, configure, and manage a NetApp® ONTAP® cluster by using the CLI and UIs such as NetApp ONTAP System Manager. Explore REST API automation for your cluster. Configure, manage, and protect block storage by using iSCSI, FC, and NVMe protocols for symmetric and asymmetric environments.

Objectives

This course focuses on enabling you to do the following:

- Identify the components of an ONTAP cluster and its features
- Examine how to manage storage provisioning and data protection
- Describe how to administratively manage an ONTAP cluster
- List ONTAP network components
- Explain storage VMs (storage virtual machines, also known as SVMs)
- Learn how SAN works in asymmetric and symmetric environments
- Configure SAN workloads in an ONTAP cluster
- Manage and protect block workloads by using ONTAP features
- Discover how to continue your ONTAP educational journey

Audience

Administrator

Programme

Module 1: SAN introduction

- ONTAP and SAN
- Storage protocols
- SAN architecture
- SAN paths

Module 2: SAN access

- Initiator setup
- Target configuration

Exercises:

- Configuring SAN access

Module 3: SAN management

- SAN mobility
- SAN resize
- SAN data protection
- SAN performance monitoring

Exercises:

- Managing block workloads

Module 4: Next steps

- Documentation
- Learning paths

Appendix 1: NVMe details

- Advantages of the NVMe protocols over the SCSI protocols

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
13 Oct 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr12,500.00

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)