



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00



Configuring & Monitoring NetApp E-Series Storage Systems

CODE:

NEP_ES-SS-CM

LENGTH:

32 Hours (4 days)

PRICE:

kr50,000.00

Description

In this course, you learn how to recommend configurations based on a pre-deployment assessment for a new NetApp E-Series or EF-Series storage system. In the deployment phase, you use both the NetApp SANtricity® storage management and system management software to create the configuration, perform administrative tasks, and employ data protection features. During post-deployment, you use SANtricity system management software to collect storage system information for trend analysis, troubleshooting, performance monitoring, and tuning.

Objectives

This course focuses on enabling you to do the following:

- Identify and use administrative and support tools for E-Series storage systems
- Install SANtricity Storage Manager software on a host platform
- Recommend and create logical configurations on E-Series storage systems
- Manage volume group and dynamic disk pools using SANtricity System Manager
- Perform routine E-Series administrative tasks using SANtricity System Manager
- Configure and administer E-Series features such as SANtricity Snapshot image, volume copy, and mirroring technologies
- Collect E-Series storage system information such as the event log, profile, and support bundle

Audience

This course is designed for Professional Services workers who are NetApp employees, NetApp partners, or NetApp customers.

Prerequisites

Basic Windows administrative experience plus technical Overview of NetApp E-Series Storage Systems

Programme

E-Series and EF-Series storage products
SANtricity management interfaces
SANtricity storage manager
SANtricity unified manager

Module 1: Introduction to E-Series and EF-Series Storage

System manager overview
Configuration and I/O Operations
Cache and battery operation
Data assurance
Media scan

Module 2: E-Series and EF-Series Functionality

Drive security
Host-Side configuration concepts
Disk-side configuration concepts
Pool and volume group configuration concepts
Initial setup steps

Module 3: Configuration Concepts and Initial Setup

Additional setup steps
Volume groups
Creating volume groups and volumes
System administration tasks

Module 4: Volume Group Administration

Managing volume group disks

Module 5: Pools Administration

Pools

Creating unsecured disk pools and volumes

Creating secure pools

System administration tasks

Managing disk pool disks

SSD Cache overview

Module 6: SSD Cache Administration

SSD Cache administration

The SANtricity Snapshot Feature

Snapshot administration

Snapshot volume operational sequences

Snapshot volume administration

Module 7: Snapshot Administration

Snapshot consistency group administration

Module 8: Copy Volume Function

Mirroring technology

Synchronous mirroring

Synchronous mirroring administration

Asynchronous mirroring

Asynchronous mirroring administration

Copy volume function overview

Copy volume administration

Module 9: Mirroring Administration

SANtricity feature considerations

Resources for collection and monitoring

Storage array component information

AutoSupport support tool

Informational files

Module 10: Data Collection and Monitoring

Performance monitoring

Module 11: General Administrative Tasks

General administrative tasks

Alert management

Storage array, controller and drive tasks

Managing upgrades

Test and Certification

This course is part of the NetApp Certified Implementation Engineer (NCIE) – SAN Specialist (E-Series) certification

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
26 Aug 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr50,000.00
13 Oct 2025	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr50,000.00

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)