

Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com Phone: +46 8 555 188 00

■ NetApp Integrating Hybrid Clouds with Microsoft Azure

CODE: LENGTH: PRICE:

NEP UNCMMAZ 16 Hours (2 days) kr26,000.00

Description

Learn to implement a hybrid cloud solution with Microsoft Azure by using NetApp® Cloud Volumes ONTAP®. Connect an Azure Virtual Network (VNet) and an on-premises data center to unify your infrastructure. Use NetApp Cloud Manager to move data and manage storage in the hybrid cloud. Learn about how NetApp cloud services are integrated into Cloud Manager to provide persistent storage for Kubernetes containers and enhance data protection, security, and compliance. Learn to optimize capacity and performance of Cloud Volumes ONTAP

Objectives

This course focuses on enabling you to do the following:

- Describe how NetApp technologies can be used to build your data fabric
- Configure a VNet and connect it to an on-premises data center with VPN Internet Protocol security (IPsec)
- Describe Cloud Volumes ONTAP architecture
- Install a Connector and deploy Cloud Volumes ONTAP
- Explain basic system administration tasks with Cloud Manager
- · Copy data between an ONTAP based system and Cloud Volumes ONTAP for Azure for disaster recovery
- Use data tiering to Azure Blob storage for Cloud Volumes ONTAP
- Use Cloud Volumes ONTAP as persistent storage for Kubernetes containers
- · Identify performance and sizing options for Cloud Volumes ONTAP

Audience

- Administrators
- Operators
- Architects
- Implementation Engineers

Prerequisites

For a successful learning experience, NetApp recommends that you know the following concepts before you attend the course.

- Cloud computing concepts Cloud characteristics, service delivery methods & cloud deployment models
- Networking concepts and definitions Classless Inter-Domain Routing (CIDR) and network address translation (NAT)
- Azure concepts Subscriptions, VNet, virtual machines (VMs), Azure storage accounts, and Azure Blob storage

Programme

Module 1: Data Fabric Overview

Lesson 1: Data Fabric

Lesson 2: Solutions for the Hybrid Cloud Lesson 3: NetApp Public Cloud Products

Lesson 4: Cloud Storage

Lesson 5: Cloud Services and Analytics

Lesson 6: Cloud Controls

Module 2: Public Cloud Essential Concepts

Lesson 1: Azure Networking and Other Concepts

Lesson 2: Terraform Introduction

Module 3: Connectivity from the Public Cloud to Other Networks

Lesson 1: Microsoft Azure VNET Connectivity to an On-Premises Network

Module 4: NetApp Cloud Manager

Lesson 1: NetApp Cloud Manager Overview

Module 5: NetApp Cloud Volumes ONTAP: Single-Node Architecture

Lesson 1: Cloud Volumes ONTAP

Lesson 2: Cloud Volumes ONTAP: Use Cases

Lesson 3: Cloud Volumes ONTAP Architecture

Lesson 4: Deploying Cloud Volumes ONTAP

Lesson 5: Cloud Volumes ONTAP Supported Features

Module 6: NetApp Cloud Volumes ONTAP: High-Availability Architecture

Lesson 1: Highly Available Cloud Volumes ONTAP in Azure

Module 7: Administration of NetApp Cloud Volumes ONTAP and NetApp Cloud Manager

Lesson 1: Administering Cloud Volumes ONTAP

Lesson 2: Administering Cloud Manager

Module 8: Implementing Disaster Recovery with NetApp Cloud Volumes ONTAP

Lesson 1: Disaster Recovery with Cloud Volumes ONTAP Overview

Module 9: Data Tiering for NetApp Cloud Volumes ONTAP

Lesson 1: Data Tiering for Cloud Volumes ONTAP Overview

Module 10: Using NetApp Cloud Manager to Provision Persistent Storage for Kubernetes Clusters

Lesson 1: Using Cloud Manager to Provision Persistent Storage for Kubernetes Cluster Overview

Module 11: Using Integrated Services from NetApp Cloud Manager

Lesson 1: Using Cloud Backup Service from Cloud Manager

Lesson 2: Using Cloud Sync from Cloud Manager

Lesson 3: Using Cloud Compliance from Cloud Manager

Lesson 4: Using Cloud Tiering Service from Cloud Manager

Module 12: Sizing NetApp Cloud Volumes ONTAP

Lesson 1: An Introduction to Sizing

Lesson 2: Capacity Sizing

Lesson 3: Performance Sizing

Lesson 4: Single Node versus High Availability

Lesson 5: Key Differences between Cloud Volumes ONTAP and On-Premises ONTAP software

Lesson 6: Performance Tuning

Lesson 7: Frequently Seen Sizing Mistakes

Test and Certification

This course is part of the following certifications:

- NetApp Certified Hybrid Cloud Architect
- NetApp Certified Hybrid Cloud Implementation Engineer
- NetApp Certified Hybrid Cloud Administrator

Session Dates

| Date | Location | Time Zone | Language | Туре | Guaranteed | PRICE |
|----------------|----------------------------|--------------|----------|--------------------------|------------|-------------|
| 10 Nov 2025 | Virtual Classroom (GMT) | GMT | English | Instructor Led Online | | kr26,000.00 |
| 15 Dec 2025 | Virtual Classroom (GMT) | GMT | English | Instructor Led Online | | kr26,000.00 |
| 29 Jan 2026 | Virtual Classroom (GMT) | GMT | English | Instructor Led Online | | kr26,000.00 |
| 07 May 2026 | Virtual Classroom (GMT) | BST | English | Instructor Led Online | | kr26,000.00 |
| 03 Sep 2026 | Virtual Classroom (GMT) | BST | English | Instructor Led Online | | kr26,000.00 |
| 05 Nov 2026 | Virtual Classroom (GMT) | GMT | English | Instructor Led Online | | kr26,000.00 |

Ytterligare information

Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.