



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00



IBM FlashSystem 9200 Implementation

CODE: SSFS7DGG **LENGTH:** 6 Hours **PRICE:** Free

Description

IBM FlashSystem 9200 system is an all-flash, powerful end-to-end Non-Volatile Memory Express (NVMe) enterprise storage solution that combines the performance of IBM FlashCore technology, the ultra-low latency of Storage Class Memory (SCM), the rich features of IBM Spectrum Virtualize, and AI predictive storage management to provide intensive, data driven multi-cloud storage for the most critical demands.

This course introduces the IBM FlashSystem 9200 control enclosures, 9846/9848 AG8 and UG8, and the IBM FlashSystem expansion enclosures, 9846/9848 AFF and A9F. It also focuses on FlashCore Technology, scalability, and RAID protection solutions.

Objectives

- Recall the history and fundamentals of the IBM Flash System storage
- Categorize the capabilities of the features of IBM Spectrum Virtualize with the IBM FlashSystem 9200
- Summarize the architecture of the IBM FlashSystem 9200
- Identify the various elements of FlashSystem 9200 Scale Up/Scale Out Solutions
- List the requirements that support intermixing cluster solutions

Audience

Enrollment in this course is not restricted. Typical students may include: Customers Technical IBM personnel Business Partner technical personnel IT consultants and architects

Programme

- Evolution of FlashSystems
- IBM Spectrum Virtualize: Improving Storage Efficiency
- IBM FlashSystem 9200 Architecture overview
- IBM FlashCore Technology
- IBM FlashSystem 9200 SAS-Attached Flash storage
- Scale up and scale out solutions
- RAID protection solutions

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
22 Nov 2024			English	Web based Training		kr2,440.00

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)