



Enterprise Computing Solutions - Education Services

## TRAINING OFFERING

---

**Du kan nå oss här**

Kronborgsgränd 7, 164 46 Kista

Email: [edu.ecs.se@arrow.com](mailto:edu.ecs.se@arrow.com)

Phone: +46 8 555 188 00



# SC-100T00: Microsoft Cybersecurity Architect

**CODE:** MCS\_SC-100T00      **LENGTH:** 32 Hours (4 days)      **PRICE:** kr30,000.00

## Description

This is an advanced, expert-level course. Although not required to attend, students are strongly encouraged to have taken and passed another associate level certification in the security, compliance and identity portfolio (such as AZ-500, SC-200 or SC-300) before attending this class. This course prepares students with the expertise to design and evaluate cybersecurity strategies in the following areas: Zero Trust, Governance Risk Compliance (GRC), security operations (SecOps), and data and applications. Students will also learn how to design and architect solutions using zero trust principles and specify security requirements for cloud infrastructure in different service models (SaaS, PaaS, IaaS).

## Audience

This course is for experienced cloud security engineers who have taken a previous certification in the security, compliance and identity portfolio. Specifically, students should have advanced experience and knowledge in a wide range of security engineering areas, including identity and access, platform protection, security operations, securing data, and securing applications. They should also have experience with hybrid and cloud implementations. Beginning students should instead take the course SC-900: Microsoft Security, Compliance, and Identity Fundamentals.  
Job role: Solution Architect

## Test and Certification

Preparation for exam: [SC-100](#)

## Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
16 Dec 2024	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr30,000.00

## Ytterligare information

Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.