



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Vous pouvez nous joindre ici

Email: training.ecs.fr@arrow.com
Phone: 01 49 97 50 00



PowerVM with PowerVC

CODE:	DURÉE:	PRIX H.T.:
AN36DG	8 Hours	€100.00

Description

This is a four hour, intermediate level, self paced learning module that describes IBM PowerVC, benefits, how to transition to using it, and how it improves Power Systems virtualization management.

Objectifs

Module 1

- Describe the history of PowerVM management
- List common LPAR management tasks
- Describe how the common LPAR management tasks are performed using the Hardware Management Console (HMC)

Module 2

- Describe the historical challenges of creating a traditional PowerVM workload

Module 3

- Compare the process of creating a PowerVM workload in PowerVC with that of the traditional HMC-based process

Module 4

- Compare traditional PowerVM management tasks with the PowerVC equivalent tasks
 - Review examples PowerVM management tasks and their PowerVC equivalents
 - Creating a PowerVM LPAR using PowerVC
 - Start an LPAR
 - Stop an LPAR
 - Perform DLPAR on an LPAR
 - Perform LPM on an LPAR
 - Delete an LPAR

Module 5

- Outline the benefits of introducing PowerVC management
- Review the requirements to implement PowerVC
- Outline the future of PowerVM management with PowerVC
- Explain the next steps on the PowerVC Learning Journey

Audience

Current or prospective PowerVM System Administrators and System Architects.

Prérequis

Basic PowerVM administration skills. No IBM course prerequisites.

Programme

- Traditional PowerVM Management
- Challenges in traditional PowerVM management
- Meeting the challenge with PowerVC
- PowerVC management of PowerVM
- Transitioning to PowerVC management of PowerVM

Dates de session

Date	Lieu	Time Zone	Langue	Type	Garanti	PRIX H.T.
28 May 2023			English	Web based Training		€100.00

Informations

Complémentaires

[Cette formation est également disponible sous forme de formation sur site. Veuillez nous contacter pour en savoir plus.](#)