



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss her

Postboks 6562 ETTERSTAD, 0606 Oslo, Norge

Email: kurs.ecs.no@arrow.com

Phone: +47 22 02 81 00



ONTAP SAN Implementation

CODE:	LENGTH:	PRICE:
NEP_OT-SANI	24 Hours (3 days)	kr28,950.00

Description

Learn how to install NetApp® ONTAP® 9 data management software for a SAN environment. Explore block-level protocols on Microsoft Windows Server and Linux host operating systems, including FC, FCoE, NVMe, and iSCSI. Apply your knowledge through hands-on guided exercises in a lab environment and through an exercise workbook that serves as an on-the-job reference guide.

Objectives

- Discuss SAN fundamentals for ONTAP software
- Explain ONTAP SAN resource provisioning
- Describe iSCSI, FC, and FCoE configuration in ONTAP software
- Explain the NVMe over Fabrics (NVMe-oF) implementation in ONTAP software
- Discuss host configuration requirements
- Explain Windows and Linux configuration for iSCSI
- Describe Windows and Linux configuration for FC

Audience

- Administrators
- Engineers
- Architects

Prerequisites

- Certification as a NetApp Data Management Administrator
- Working knowledge of ONTAP 9 software and storage area networking
- ONTAP Cluster Fundamentals via NetApp Learning Centre
- ONTAP SAN Fundamentals via NetApp Learning Centre
- ONTAP Cluster Administration via NetApp Learning Centre

Programme

- Classroom logistics
- Course prerequisites

Module 0: Introduction • Course agenda

- Implementing iSCSI, FCP, FCoE, and NVMe-oF SAN in ONTAP software
- SAN architecture
- Interoperability Matrix Tool
- SAN scalability and maximums
- IP SAN configurations
- FC SAN configurations
- LUN provisioning

Module 1: ONTAP SAN fundamentals

- FC configuration recommendations
- FC and FCoE zoning
- Cisco switches

Module 3: ONTAP iSCSI configuration concepts

- Brocade switches

Module 2: ONTAP SAN resource provisioning

- iSCSI configuration recommendations
- iSCSI feature overview

Module 4: ONTAP FC configuration concepts

- iSCSI configuration workflow

Module 5: NVMe-oF configuration

- NVMe
- NVMe-oF
- NVMe integration into ONTAP software
- Host considerations
- Windows hosts
- Linux and UNIX hosts
- LUN offset
- Configuring a Windows host for iSCSI
- iSCSI configuration
- Linux iSCSI configuration
- Linux iSCSI implementation
- Linux iSCSI implementation
- Configuring a Windows host for FC
- Identifying the WWNN and WWPN on a Windows host
- Implementing and verifying multipath FC connectivity between a Windows host and ONTAP software
- Configuring a Linux host for FC
- Identifying WWNPs on a Linux host
- Implementing and verifying multipath FC connectivity between a Linux host and ONTAP software

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
09 Dec 2024	Virtual Classroom (CET / UTC +1)	CET	English	Instructor Led Online		kr28,950.00

Tilleggsinformasjon

Denne treningen er også tilgjengelig som trening på stedet. [Kontakt oss for å finne ut mer.](#)