



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå os her

Email: training.ecs.dk@arrow.com
Phone: +45 7025 4500

CODE:	LENGTH:	PRICE:
VMW_SCT	32 Hours (4 dage)	kr 22,380.00

Description

This 4-day course offers hands-on experience with the major features of Spring and Spring Boot, which includes configuration, data access, REST, AOP, auto-configuration, actuator, security, and Spring testing framework to build enterprise and microservices applications. On completion, participants will have a foundation for creating enterprise and cloud-ready applications. This course prepares students for the Spring Professional certification exam.

Objectives

By the end of the course, you should be able to meet the following objectives:

- Spring configuration using Java Configuration and Annotations
- Aspect oriented programming with Spring
- Testing Spring applications using JUnit 5
- Spring Data Access - JDBC, JPA and Spring Data
- Spring Transaction Management
- Simplifying application development with Spring Boot
- Spring Boot auto-configuration, starters and properties
- Build a simple REST application using Spring Boot, embedded Web Server and fat JARs or classic WARs
- Implementing REST client applications using RestTemplate and WebClient
- Spring Security
- Enable and extend metrics and monitoring capabilities using Spring Boot actuator
- Utilize Spring Boot enhancements to testing

Audience

Application developers who want to increase their understanding of Spring and Spring Boot with hands-on experience and a focus on fundamentals.

Prerequisites

Some developer experience using Java, an IDE (Eclipse, STS or IntelliJ) and build tools such as Maven or Gradle

Programme

1 Introduction to Spring

- Java configuration and the Spring application context
- @Configuration and @Bean annotations
- @Import: working with multiple configuration files
- Defining bean scopes
- Launching a Spring Application and obtaining Beans

2 Spring JAVA Configuration: A Deeper Look

- External properties & Property sources
- Environment abstraction

- • Using bean profiles
- • Spring Expression Language (SpEL)

3 Annotation-based Dependency Injection

- • Component scanning
- • Autowiring using `@Autowired`
- • Java configuration versus annotations, mixing.
- • Lifecycle annotations: `@PostConstruct` and `@PreDestroy`
- • Stereotypes and meta-annotations

4 Factory Pattern in Spring

- • Using Spring `FactoryBeans`

5 Advanced Spring: How Does Spring Work Internally?

- • The Spring Bean Lifecycle
- • The `BeanFactoryPostProcessor` interception point
- • The `BeanPostProcessor` interception point
- • Spring Bean Proxies
- • `@Bean` method return types

6 Aspect-oriented programming

- • What problems does AOP solve?
- • Defining pointcut expressions
- • Implementing various types of advice

7 Testing a Spring-based Application

- • Spring and Test-Driven Development
- • Spring 5 integration testing with JUnit 5
- • Application context caching and the `@DirtiesContext` annotation
- • Profile selection with `@ActiveProfiles`
- • Easy test data setup with `@Sql`

8 Data Access and JDBC with Spring

- • How Spring integrates with existing data access technologies
- • `DataAccessException` hierarchy
- • Spring's `JdbcTemplate`

9 Database Transactions with Spring

- • Transactions overview
- • Transaction management with Spring
- • Transaction propagation and rollback rules
- • Transactions and integration testing

10 Spring Boot Introduction

- • Introduction to Spring Boot Features
- • Value Proposition of Spring Boot
- • Creating a simple Boot application using Spring Initializer website

11 Spring Boot Dependencies, Auto-configuration, and Runtime

- • Dependency management using Spring Boot starters
- • How auto-configuration works
- • Configuration properties
- • Overriding auto-configuration
- • Using `CommandLineRunner`

12 JPA with Spring and Spring Data

- • Quick introduction to ORM with JPA
- • Benefits of using Spring with JPA
- • JPA configuration in Spring
- • Configuring Spring JPA using Spring Boot
- • Spring Data JPA dynamic repositories

13 Spring MVC Architecture and Overview

- • Introduction to Spring MVC and request processing
- • Controller method signatures
- • Using @Controller, @RestController and @GetMapping annotations
- • Configuring Spring MVC with Spring Boot
- • Spring Boot packaging options, JAR or WAR

14 Rest with Spring MVC

- • An introduction to the REST architectural style
- • Controlling HTTP response codes with @ResponseStatus
- • Implementing REST with Spring MVC, @RequestMapping, @RequestBody and @ResponseBody
- •

Spring MVC's HttpMessageConverters and automatic content negotiation 15 Spring Security

- • What problems does Spring Security solve?
- • Configuring authentication
- • Implementing authorization by intercepting URLs
- • Authorization at the Java method level
- • Understanding the Spring Security filter chain
- • Spring security testing

16 Actuators, Metrics and Health Indicators

- • Exposing Spring Boot Actuator endpoints
- • Custom Metrics
- • Health Indicators
- • Creating custom Health Indicators
- • External monitoring systems

17 Spring Boot Testing Enhancements

- • Spring Boot testing overview
- • Integration testing using @SpringBootTest
- • Web slice testing with MockMvc framework
- • Slices to test different layers of the application

18 Spring Security OAuth (Optional Topic)

- • OAuth 2 Overview
- • Implementing OAuth 2 using Spring Security OAuth

19 Reactive Applications with Spring (Optional Topic)

- • Overview of Reactive Programming concepts
- • Reactive Programming support in Spring
- • Using Spring's reactive WebClient

Session Dates

På anmodning. [Kontakt os venligst](#)

Yderligere Information

[Denne træning er også tilgængelig som træning på stedet. Kontakt os for at finde ud af mere.](#)