



Enterprise Computing Solutions - Education Services

OFERTA FORMATIVA

Detalles de contacto

Avda Europa 21, 28108 Alcobendas

Email: formacion.ecs.es@arrow.com

Phone: +34 91 761 21 51



ONTAP SAN Implementation 9.8

CÓDIGO:

NEP_OT-SANI 9.8

DURACIÓN:

24 Hours (3 días)

Precio:

€2,850.00

Description

In this course, you learn the installation process for NetApp® ONTAP® 9 data management software for a SAN environment. The course provides information about block-level protocols, including FC, FCoE, NVMe, and iSCSI, on Microsoft Windows Server, Linux, and VMware ESXi host operating systems. The learning is reinforced through hands-on guided exercises. The course materials include a workbook that serves as an on-the-job reference guide.

Objetivos

- Define and describe SAN environments that use iSCSI, FC, FCoE, and NVMe protocols
- Examine FC switch fabric, LUN masking, and zoning
- Create and configure storage VMs (storage virtual machines, also known as SVMs) to use FC and iSCSI protocols
- Configure Microsoft Windows Server, Red Hat Enterprise Linux, and ONTAP systems for iSCSI connectivity
- Configure Microsoft Windows Server, Red Hat Enterprise Linux, and ONTAP systems for FC connectivity
- Create and access a LUN from a Windows Server and a Red Hat Enterprise Linux server

Público

Professionals who implement SAN solutions that use NetApp storage systems

Requisitos Previos

- Certification as a NetApp Data Management Administrator
- Working knowledge of ONTAP 9 software and storage area networking
- Completion of the following courses:
 - ONTAP Cluster Fundamentals
 - ONTAP SAN Fundamentals
 - ONTAP Cluster Administration

Fechas Programadas

A petición. Gracias por [contactarnos](#).

Información Adicional

[Esta formación también está disponible en modalidad presencial. Por favor contáctenos para más información.](#)