



Enterprise Computing Solutions - Education Services

## TRAINING OFFERING

---

**Du kan nå oss her**

Postboks 6562 ETTERSTAD, 0606 Oslo, Norge

Email: [kurs.ecs.no@arrow.com](mailto:kurs.ecs.no@arrow.com)

Phone: +47 22 02 81 00



# IBM DS8000 Implementation Workshop for z Systems

<b>CODE:</b>	<b>LENGTH:</b>	<b>PRICE:</b>
SSF1G	24 Hours (3 days)	kr23,655.00

## Description

To learn the DS8000 storage subsystem and its hardware components and logical structure. You configure the DS8000 storage subsystem using a DS8000 Storage Manager GUI and review the DS CLI interface for scripting configuration functions. You will also perform dynamic data relocation using Easy Tier function. In addition we have a unit on the recently announced product called the DS8900F.

## Objectives

- Using the history, hardware & software features, functions, and components of the DS8000 family determine the architecture of the DS8880
- Distinguish those elements that contribute to virtualization and the DS8880
- Carry out those steps needed to configure the DS8880, using the Data Storage Command Line Interface (DS CLI)
- Carry out those steps needed to configure the DS8880, using the data storage Graphical User Interface (GUI)
- Outline those benefits of host attachments that will enable higher throughput and lower response times when connecting a DS8880 to your z System
- Clarify the features of cache, performance identification, and TPC and their contributions to the physical and logical setup of the DS8880
- Relate those functions of copy services, flash copy, and global mirroring to business continuity
- Summarize the features and functions of the DS8900F Distinguish the benefits of the three DS8900F models

## Audience

This course is for system administrators, architects, and storage specialists. Anyone who needs to learn about DS8000 implementation and experiment with them on a real test configuration.

## Prerequisites

You should have completed:

Introduction to Storage (*SS01G*) An understanding of DASD and data sets and how clients hosts access directly or through FICON channels.

## Programme

- Day 1
  - Welcome Unit 1: Concepts and architecture Unit 2: Concepts of virtualization Unit 3: DS Command Line Interface Exercise 0: Lab setup and preliminary instructions Exercise 1: DS8000 DS CLI: Installation and configuration Exercise 2: DS8000 DS CLI: DDMs, array sites, arrays, ranks, and extent pools Exercise 3: DS8000 DS CLI: LCU, CKD volumes, and PAVs
- Day 2
  - Unit 4: DS8000 Storage Manager GUI Exercise 4: DS8000 Storage Manager: Arrays, ranks, and extent pools Exercise 5: DS8000 Storage Manager: LCU, CKD volumes, and PAVs Exercise 6: DS8000 Storage Manager: I/O ports configuration Exercise 7: DS8000 Storage Manager: Other functions Exercise 8: DS8000 Easy Tier: Dynamic volume relocation
- Day 3
  - Exercise 9: DS8000 Easy Tier: Dynamic pool merge Unit 5: Host attachment Unit 6: Performance, tuning, and monitoring Unit 7: Business continuity
  - Unit 8: DS8900F Introduction

## Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
14 Oct 2024	Virtual Classroom (CET / UTC +1)	CEDT	English	Instructor Led Online		kr23,655.00

## Tilleggsinformasjon

Denne treningen er også tilgjengelig som trening på stedet. Kontakt oss for å finne ut mer.