



## TRAINING OFFERING

---

**You can reach us at:**

Arrow ECS, Nidderdale House, Beckwith Knowle, Harrogate, HG3 1SA

Email: [educationteam.ecs.uk@arrow.com](mailto:educationteam.ecs.uk@arrow.com)

Phone: 0870 251 1000



# IBM Cloud Application Performance Management

## 8.1.4 Fundamentals

CODE:	LENGTH:	PRICE:
TOD51G	3 day(s)	£950.00

### Description

This course teaches new and experienced operators, administrators, and implementers of Application Performance Management v8.1.4 how to effectively use the tools to manage their enterprise monitoring needs. IBM Cloud Application Performance Management v8.1.4 monitors the performance and availability of computer operating systems and applications

In this course, you learn about the IBM Cloud Application Performance Management architecture and how to install and configure the product. You also learn how to navigate the Cloud APM console to manage events and user access privileges. The course also covers integration with other products, such as Netcool/OMNIBus, IBM Tivoli Monitoring, and the Dashboard Application Services Hub.

The lab environment for this course uses the RHEL 7.3 and Windows 2012 Server platforms.

For information about other related courses, visit the IBM Training website: <http://www.ibm.com/training>

If you are enrolling in a Self Paced Virtual Classroom or Web Based Training course, before you enroll, please review the Self-Paced Virtual Classes and Web-Based Training Classes on our Terms and Conditions page, as well as the system requirements, to ensure that your system meets the minimum requirements for this course. <http://www.ibm.com/training/terms>

### Objectives

After completing this course, you should be able to:

- Describe the overall solution
- Install and configure the Cloud APM server
- Install, configure, and manage operating system agents
- Administer Cloud APM, including:
  - Applications
  - Users
  - Groups
  - Custom views
  - LDAP integration
- Monitor events
- Deploy and monitor the end user experience
- Deploy and monitor applications with synthetic transactions
- Deploy and monitor application resources
- Track transactions through application components
- Configure and perform deep-dive request analysis
- Integrate Cloud APM with other solutions
- Configure and generate reports

### Audience

This course is designed for operators, administrators, and implementers.

### Prerequisites

Before taking this course, you should be able to navigate Linux and Windows applications, and have a working knowledge of an Internet browser.

## Programme

Course introduction  
Introduction to IBM Cloud Application Performance Management  
Cloud APM server installation  
Installing, configuring, and managing Cloud APM agents  
Administration  
Monitoring events  
Monitoring the end user experience of applications  
Monitoring applications with synthetic transactions  
Monitoring resources  
Tracking transactions through application components  
Introduction to deep-dive diagnosis  
Integrating Cloud APM with other products  
Reporting and 7-day comparison

## Further Information

Prior to enrolling, IBM Employees must follow their Division/Department processes to obtain approval to attend this public training class. Failure to follow Division/Department approval processes may result in the IBM Employee being personally responsible for the class charges.

GBS practitioners that use the EViTA system for requesting external training should use that same process for this course. Go to the EViTA site to start this process:

<http://w3.ibm.com/services/gbs/evita/BCSVTEenrl.nsf>

Once you enroll in a GTP class, you will receive a confirmation letter that should show:

- The current GTP list price
- The 20% discounted price available to IBMers. This is the price you will be invoiced for the class.

## Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
10 Aug 2022			English	Self Paced Training		£950.00

## Additional Information

[This training is also available as onsite training. Please contact us to find out more.](#)