



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå os her

Email: training.ecs.dk@arrow.com
Phone: +45 7025 4500



InfoSphere MDM Virtual Foundation V11.4

CODE:	LENGTH:	PRICE:
ZZ720G	24 Hours (3 dage)	kr 17,460.00

Description

This course is designed as the starting point for any technical specialist working with the InfoSphere MDM Virtual module. This course walks you through the major components of the InfoSphere MDM Virtual module, the data model, the matching engine and how customization can be implemented. You will learn how to invoke the InfoSphere MDM interactions and the various configuration and extension points of a service. The course is also used as an intro to various components that make up the MDM Architecture and prepares you to identify how the MDM will fit into their organization and what pieces may be customize to fit their business requirements.

This course has a heavy emphasis on the exercises, where you will deploy a new MDM configuration, invoke interactions, walk through the default matching algorithm, and create a custom handler and composite view.

At the end of this course, it is expected that you will feel comfortable implementing a new Virtual configuration data model, invoking interactions and creating customization to the Virtual MDM.

Objectives

- Understand the InfoSphereVirtual MDM Architecture and how an interaction on the Virtual MDM are handled
- Understand the Configuration Points of the InfoSphere MDM
- Understand the Tables of the Virtual MDM
- Understand the Configuration Points of the InfoSphere MDM Virtual Hub
- Understand the Common components Virtual MDM

Audience

This intermediate course is for technical specialist who will be developing a solution using the InfoSphere MDM Virtual Module.

Prerequisites

There are no prerequisites to this course.

Programme

Unit 1: MDM and the Enterprise

- MDM Overview and Scenarios
- MDM implementation stypes
- Virtual and Physical Modules

Unit 2: Architecture

- InfoSphere MDM Architecture and Components
- Core Processes

Unit 3: MDM Virtual Data Model

- Metadata
- Member Tables
- Entity Tables
- Relationships

- Audit Tables
- Tasks

Unit 4: How InfoSphere MDM services are Invoked

- Java API and Web Services
- Brokers
- eSOA Toolkit
- REST Interface
- Master Data Extract

Unit 5: Linking and Duplicates

- Probabilistic Matching Engine
- Algorithms
- Weights
- Virtual Module Linking

Unit 6: How Services are Configured (Virtual)

- Event Notifications
- Callout Handlers
- Composite Views

Unit 7: Other Components

- Login and Serviceability
- Quality Stage Standardization
- Security
- Hybrid
- Application Toolkit

Agenda :Day 1

- Unit 1: MDM and the Enterprise
- Unit 2: Architecture
- Unit 3: MDM Virtual Model

Day 2

- Unit 4: How InfoSphere MDM services are Invoked
- Unit 5: Linking and Duplicates

Day 3

- Unit 6: How Services are Configured
- Unit 7: Other Components

Further Information

Prior to enrolling, IBM Employees must follow their Division/Department processes to obtain approval to attend this public training class. Failure to follow Division/Department approval processes may result in the IBM Employee being personally responsible for the class charges.

GBS practitioners that use the EViTA system for requesting external training should use that same process for this course. Go to the EViTA site to start this process: <http://w3.ibm.com/services/gbs/evita/BCSVTEnr1.nsf>

Once you enroll in a GTP class, you will receive a confirmation letter that should show:

- The current GTP list price
- The 20% discounted price is available to IBMers for GTP delivered courses only. This is the price you will be invoiced for the class.

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
31 Jul 2023	Virtual Classroom (GMT / UTC)	BST	English	Instructor Led Online		kr 17,460.00
23 Oct 2023	Virtual Classroom (GMT / UTC)	BST	English	Instructor Led Online		kr 17,460.00

Yderligere Information

[Denne træning er også tilgængelig som træning på stedet. Kontakt os for at finde ud af mere.](#)