



Enterprise Computing Solutions - Education Services

TRAINING OFFERING

Du kan nå oss här

Kronborgsgränd 7, 164 46 Kista

Email: edu.ecs.se@arrow.com

Phone: +46 8 555 188 00



Integrating Hybrid Clouds with Amazon Web Services (38 Training Units)

CODE:	LENGTH:	PRICE:
NEP_UNCMMAZ	3 days	kr26,400.00

Description

Learn to implement a hybrid cloud solution with Microsoft Azure by using NetApp® Cloud Volumes ONTAP®. Connect an Azure Virtual Network (VNet) and an on-premises data center to unify your infrastructure. Use NetApp Cloud Manager to move data and manage storage in the hybrid cloud. Learn about how NetApp cloud services are integrated into Cloud Manager to provide persistent storage for Kubernetes containers and enhance data protection, security, and compliance. Learn to optimize capacity and performance of Cloud Volumes ONTAP.

Objectives

- Describe how NetApp technologies can be used to build your data fabric
- Configure a VNet and connect it to an on-premises data center with VPN Internet Protocol security (IPsec)
- Describe Cloud Volumes ONTAP architecture
- Install a Connector and deploy Cloud Volumes ONTAP
- Explain basic system administration tasks with Cloud Manager
- Copy data between an ONTAP based system and Cloud Volumes ONTAP for Azure for disaster recovery
- Use data tiering to Azure Blob storage for Cloud Volumes ONTAP
- Use Cloud Volumes ONTAP as persistent storage for Kubernetes containers
- Identify performance and sizing options for Cloud Volumes ONTAP

Audience

Administrators, operators, architects, and implementation engineers

Prerequisites

For a successful learning experience, NetApp recommends that you know the following concepts before you attend the course.

- **Cloud computing concepts:**
Cloud characteristics, service delivery methods, and cloud deployment models
- **Networking concepts and definitions:**
Classless Inter-Domain Routing (CIDR) and network address translation (NAT)
- **Azure concepts:**
Subscriptions, VNet, virtual machines (VMs), Azure storage accounts, and Azure Blob storage

Session Dates

Date	Location	Time Zone	Language	Type	Guaranteed	PRICE
24 Jan 2022	Virtual Classroom (GMT)	GMT	English	Instructor Led Online	Yes	kr26,400.00
07 Mar 2022	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr26,400.00
04 Apr 2022	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr26,400.00
23 May 2022	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr26,400.00
13 Jun 2022	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr26,400.00
25 Jul 2022	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr26,400.00
22 Aug 2022	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr26,400.00
19 Sep 2022	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr26,400.00
03 Oct 2022	Virtual Classroom (GMT)	BST	English	Instructor Led Online		kr26,400.00
21 Nov 2022	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr26,400.00
05 Dec 2022	Virtual Classroom (GMT)	GMT	English	Instructor Led Online		kr26,400.00

Ytterligare information

[Denna utbildning finns också som utbildning på plats. Kontakta oss för mer information.](#)